

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284086

Luminaire Tested: P3AS09R65B2750DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284086
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65B2750DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 80CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 242.0 lumens
Efficiency: N/A
Efficacy: 18.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284086

CATALOG NUMBER: P3AS09R65B2750DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284086

CATALOG NUMBER: P3AS09R65B2750DE010 E3DLD1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43067
5°	42483
10°	41059
15°	38729
20°	35726
25°	32421
30°	28713
35°	24440
40°	19436
45°	13738
50°	7983
55°	4358
60°	4035
65°	3684
70°	3334
75°	3135
80°	2778
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13738 cd/sqm

TEST NUMBER: P1284086

CATALOG NUMBER: P3AS09R65B2750DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	7.5
10°-20°	47.7	19.7
20°-30°	61.3	25.3
30°-40°	56.7	23.4
40°-50°	34.3	14.2
50°-60°	11.7	4.8
60°-70°	7.0	2.9
70°-80°	4.0	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	127.2	52.6
0°-40°	184.0	76.0
0°-60°	229.9	95.0
0°-90°	242.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	242.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	196	
5°	193	18
15°	171	48
25°	134	61
35°	91	57
45°	44	34
55°	11	12
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1284086

CATALOG NUMBER: P3AS09R65B2750DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	196.4
2.5°	195.5
5°	193.0
7.5°	189.3
10°	184.4
12.5°	178.3
15°	170.6
17.5°	162.3
20°	153.1
22.5°	143.5
25°	134.0
27.5°	123.9
30°	113.4
32.5°	103.0
35°	91.3
37.5°	79.9
40°	67.9
42.5°	55.9
45°	44.3
47.5°	33.5
50°	23.4
52.5°	14.8
55°	11.4
57.5°	10.1
60°	9.2
62.5°	8.0
65°	7.1
67.5°	6.1
70°	5.2
72.5°	4.6
75°	3.7
77.5°	3.1
80°	2.2
82.5°	1.5
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)