

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285106

Luminaire Tested: P3AS13R40B2750DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285106
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40B2750DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 80CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 360.0 lumens
Efficiency: N/A
Efficacy: 18.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285106
CATALOG NUMBER: P3AS13R40B2750DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285106
 CATALOG NUMBER: P3AS13R40B2750DE010 E3DLD1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80805
5°	79353
10°	74793
15°	67946
20°	59692
25°	50955
30°	42209
35°	32551
40°	23186
45°	15599
50°	8529
55°	6002
60°	5657
65°	5241
70°	4616
75°	4406
80°	3536
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15599 cd/sqm



TEST NUMBER: P1285106
 CATALOG NUMBER: P3AS13R40B2750DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.6	9.3
10°-20°	83.4	23.2
20°-30°	96.4	26.8
30°-40°	75.9	21.1
40°-50°	39.0	10.8
50°-60°	14.9	4.1
60°-70°	9.9	2.7
70°-80°	5.3	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	213.3	59.3
0°-40°	289.3	80.4
0°-60°	343.2	95.3
0°-90°	360.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	360.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	368	
5°	360	34
15°	299	83
25°	211	96
35°	122	76
45°	50	39
55°	16	15
65°	10	10
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1285106
CATALOG NUMBER: P3AS13R40B2750DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	368.5
2.5°	366.5
5°	360.5
7.5°	350.0
10°	335.9
12.5°	319.4
15°	299.3
17.5°	278.3
20°	255.8
22.5°	232.8
25°	210.6
27.5°	188.5
30°	166.7
32.5°	144.6
35°	121.6
37.5°	100.3
40°	81.0
42.5°	64.4
45°	50.3
47.5°	36.7
50°	25.0
52.5°	18.1
55°	15.7
57.5°	14.1
60°	12.9
62.5°	11.3
65°	10.1
67.5°	8.5
70°	7.2
72.5°	6.0
75°	5.2
77.5°	4.0
80°	2.8
82.5°	2.4
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)