

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284146

Luminaire Tested: P3AS09R70B2750DE010 E3CB1MB_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70B2750DE010 E3CB1MB_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 80CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 784.0 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284146

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MB_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284146

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MB_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78		
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155689
5°	148558
10°	141347
15°	137549
20°	132475
25°	125378
30°	116626
35°	97949
40°	63147
45°	29336
50°	7710
55°	1912
60°	1930
65°	1608
70°	1603
75°	1610
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29336 cd/sqm

TEST NUMBER: P1284146

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MB_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	8.1
10°-20°	170.3	21.7
20°-30°	237.9	30.3
30°-40°	220.6	28.1
40°-50°	79.1	10.1
50°-60°	6.7	0.9
60°-70°	3.3	0.4
70°-80°	2.2	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.3	60.1
0°-40°	691.9	88.2
0°-60°	777.7	99.2
0°-90°	784.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	784.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	710	
5°	675	63
15°	606	170
25°	518	238
35°	366	221
45°	95	79
55°	5	7
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1284146

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MB_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	710.0
2.5°	699.3
5°	674.9
7.5°	652.3
10°	634.8
12.5°	620.4
15°	605.9
17.5°	588.4
20°	567.7
22.5°	543.9
25°	518.2
27.5°	491.9
30°	460.6
32.5°	420.5
35°	365.9
37.5°	296.4
40°	220.6
42.5°	150.4
45°	94.6
47.5°	52.6
50°	22.6
52.5°	7.5
55°	5.0
57.5°	4.4
60°	4.4
62.5°	3.8
65°	3.1
67.5°	3.1
70°	2.5
72.5°	2.5
75°	1.9
77.5°	1.9
80°	1.3
82.5°	1.3
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)