

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285123

Luminaire Tested: P3AS13R40B2750DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40B2750DE010 E3DLD1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 676.0 lumens
Efficiency: N/A
Efficacy: 35.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285123

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285123

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151742
5°	148998
10°	140456
15°	127560
20°	112080
25°	95715
30°	79278
35°	61141
40°	43510
45°	29305
50°	15999
55°	11278
60°	10613
65°	9806
70°	8719
75°	8303
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 29305 cd/sqm

TEST NUMBER: P1285123

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	9.3
10°-20°	156.5	23.2
20°-30°	181.0	26.8
30°-40°	142.6	21.1
40°-50°	73.2	10.8
50°-60°	28.0	4.1
60°-70°	18.5	2.7
70°-80°	10.1	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	400.6	59.3
0°-40°	543.2	80.4
0°-60°	644.4	95.3
0°-90°	676.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	676.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	692	
5°	677	63
15°	562	157
25°	396	181
35°	228	143
45°	94	73
55°	30	28
65°	19	19
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1285123

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	692.0
2.5°	688.2
5°	676.9
7.5°	657.2
10°	630.8
12.5°	599.8
15°	561.9
17.5°	522.6
20°	480.3
22.5°	437.1
25°	395.6
27.5°	354.0
30°	313.1
32.5°	271.5
35°	228.4
37.5°	188.3
40°	152.0
42.5°	121.0
45°	94.5
47.5°	68.8
50°	46.9
52.5°	34.0
55°	29.5
57.5°	26.5
60°	24.2
62.5°	21.2
65°	18.9
67.5°	15.9
70°	13.6
72.5°	11.3
75°	9.8
77.5°	7.6
80°	5.3
82.5°	4.5
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)