

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284148

Luminaire Tested: P3AS09R70B2750DE010 E3CB1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284148
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70B2750DE010 E3CB1MMS_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 722.0 lumens
Efficiency: N/A
Efficacy: 55.1 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284148

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MMS_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284148

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143366
5°	136804
10°	130169
15°	126675
20°	121997
25°	115458
30°	107384
35°	90212
40°	58137
45°	27011
50°	7096
55°	1759
60°	1754
65°	1505
70°	1475
75°	1440
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27011 cd/sqm

TEST NUMBER: P1284148

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.2	8.1
10°-20°	156.8	21.7
20°-30°	219.1	30.3
30°-40°	203.1	28.1
40°-50°	72.8	10.1
50°-60°	6.1	0.9
60°-70°	3.1	0.4
70°-80°	2.0	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.0	60.1
0°-40°	637.2	88.2
0°-60°	716.1	99.2
0°-90°	722.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	722.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	654	
5°	622	58
15°	558	157
25°	477	219
35°	337	203
45°	87	73
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1284148

CATALOG NUMBER: P3AS09R70B2750DE010 E3CB1MMS_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	653.8
2.5°	644.0
5°	621.5
7.5°	600.7
10°	584.6
12.5°	571.3
15°	558.0
17.5°	541.9
20°	522.8
22.5°	500.9
25°	477.2
27.5°	453.0
30°	424.1
32.5°	387.2
35°	337.0
37.5°	273.0
40°	203.1
42.5°	138.5
45°	87.1
47.5°	48.5
50°	20.8
52.5°	6.9
55°	4.6
57.5°	4.0
60°	4.0
62.5°	3.5
65°	2.9
67.5°	2.9
70°	2.3
72.5°	2.3
75°	1.7
77.5°	1.7
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)