

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285132

Luminaire Tested: P3AS13R40B2750DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40B2750DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 276.0 lumens
Efficiency: N/A
Efficacy: 14.5 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285132

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285132

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92	89	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86	84	81	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	79	76	74
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77	74	71	69
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73	69	66	65
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70	66	62	61
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66	62	59	58
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63	59	56	54
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85936
5°	84195
10°	78400
15°	68332
20°	55071
25°	41277
30°	29017
35°	19006
40°	11507
45°	6884
50°	4094
55°	3288
60°	2982
65°	2542
70°	2436
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6884 cd/sqm

TEST NUMBER: P1285132

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.5	12.9
10°-20°	82.9	30.0
20°-30°	78.1	28.3
30°-40°	45.2	16.4
40°-50°	18.0	6.5
50°-60°	8.0	2.9
60°-70°	4.9	1.8
70°-80°	2.6	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.6	71.2
0°-40°	241.7	87.6
0°-60°	267.7	97.0
0°-90°	276.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	276.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	392	
5°	382	36
15°	301	83
25°	171	78
35°	71	45
45°	22	18
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1285132

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	391.9
2.5°	389.7
5°	382.5
7.5°	369.4
10°	352.1
12.5°	328.8
15°	301.0
17.5°	269.8
20°	236.0
22.5°	202.2
25°	170.6
27.5°	141.3
30°	114.6
32.5°	91.3
35°	71.0
37.5°	53.7
40°	40.2
42.5°	30.1
45°	22.2
47.5°	16.2
50°	12.0
52.5°	9.8
55°	8.6
57.5°	7.9
60°	6.8
62.5°	5.6
65°	4.9
67.5°	4.1
70°	3.8
72.5°	3.0
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)