

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284201

Luminaire Tested: P3AS09R70B2750DE010 E3DL1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70B2750DE010 E3DL1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 80CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 309.0 lumens
Efficiency: N/A
Efficacy: 23.6 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284201

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284201

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59820
5°	59102
10°	57403
15°	54961
20°	51478
25°	46769
30°	40411
35°	32203
40°	23444
45°	15412
50°	7232
55°	2217
60°	2149
65°	2075
70°	1988
75°	2118
80°	1894
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15412 cd/sqm

TEST NUMBER: P1284201

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.3	8.2
10°-20°	67.8	21.9
20°-30°	88.1	28.5
30°-40°	74.7	24.2
40°-50°	38.5	12.5
50°-60°	7.4	2.4
60°-70°	4.0	1.3
70°-80°	2.5	0.8
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.1	58.6
0°-40°	255.8	82.8
0°-60°	301.8	97.7
0°-90°	309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	309.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	273	
5°	268	25
15°	242	68
25°	193	88
35°	120	75
45°	50	39
55°	6	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1284201

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	272.8
2.5°	271.9
5°	268.5
7.5°	263.6
10°	257.8
12.5°	250.4
15°	242.1
17.5°	232.0
20°	220.6
22.5°	207.7
25°	193.3
27.5°	177.1
30°	159.6
32.5°	140.2
35°	120.3
37.5°	100.7
40°	81.9
42.5°	64.4
45°	49.7
47.5°	36.5
50°	21.2
52.5°	9.2
55°	5.8
57.5°	5.5
60°	4.9
62.5°	4.6
65°	4.0
67.5°	3.7
70°	3.1
72.5°	2.8
75°	2.5
77.5°	1.8
80°	1.5
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)