

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284205

Luminaire Tested: P3AS09R70B2750DE010 E3DL1H_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70B2750DE010 E3DL1H_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 80CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 591.0 lumens
Efficiency: N/A
Efficacy: 45.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284205

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1H_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284205

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1H_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90	88	86	84
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84	81	79	77
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79	75	72	70
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74	70	66	65
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69	65	61	60
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65	60	57	55
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61	56	53	51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49	48
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54	49	46	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114421
5°	113031
10°	109773
15°	105131
20°	98475
25°	89473
30°	77278
35°	61596
40°	44855
45°	29491
50°	13816
55°	4282
60°	4122
65°	3943
70°	3783
75°	3982
80°	3662
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29491 cd/sqm

TEST NUMBER: P1284205

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1H_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	8.2
10°-20°	129.6	21.9
20°-30°	168.4	28.5
30°-40°	142.9	24.2
40°-50°	73.7	12.5
50°-60°	14.2	2.4
60°-70°	7.7	1.3
70°-80°	4.7	0.8
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	346.4	58.6
0°-40°	489.3	82.8
0°-60°	577.2	97.7
0°-90°	591.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	591.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	522	
5°	514	48
15°	463	130
25°	370	168
35°	230	143
45°	95	74
55°	11	14
65°	8	8
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1284205

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1H_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	521.8
2.5°	520.0
5°	513.5
7.5°	504.2
10°	493.0
12.5°	478.9
15°	463.1
17.5°	443.7
20°	422.0
22.5°	397.3
25°	369.8
27.5°	338.6
30°	305.2
32.5°	268.2
35°	230.1
37.5°	192.5
40°	156.7
42.5°	123.3
45°	95.1
47.5°	69.8
50°	40.5
52.5°	17.6
55°	11.2
57.5°	10.6
60°	9.4
62.5°	8.8
65°	7.6
67.5°	7.0
70°	5.9
72.5°	5.3
75°	4.7
77.5°	3.5
80°	2.9
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)