

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284210

Luminaire Tested: P3AS09R70B2750DE010 E3DL1LI\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1284210  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R70B2750DE010 E3DL1LI\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 4000K CCT AND, 80CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 591.0 lumens  
Efficiency: N/A  
Efficacy: 45.1 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1284210

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1LI\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1284210

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1LI\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 |  | 100 | 98  | 97  |  | 96  | 95  | 94  | 92  |
| 2   | 106 | 101 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 92  | 90  |  | 93  | 90  | 88  |  | 90  | 88  | 86  | 84  |
| 3   | 100 | 93  | 88  | 83  | 98  | 92  | 87  | 82  | 89  | 85  | 81  |  | 86  | 83  | 80  |  | 84  | 81  | 79  | 77  |
| 4   | 94  | 86  | 80  | 75  | 93  | 85  | 79  | 75  | 83  | 78  | 74  |  | 81  | 76  | 73  |  | 79  | 75  | 72  | 70  |
| 5   | 89  | 80  | 73  | 69  | 87  | 79  | 73  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  | 70  | 66  | 65  |
| 6   | 84  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 61  | 60  |
| 7   | 79  | 69  | 62  | 58  | 78  | 68  | 62  | 58  | 67  | 61  | 57  |  | 66  | 61  | 57  |  | 65  | 60  | 57  | 55  |
| 8   | 75  | 65  | 58  | 53  | 74  | 64  | 58  | 53  | 63  | 57  | 53  |  | 62  | 57  | 53  |  | 61  | 56  | 53  | 51  |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  |  | 58  | 53  | 49  |  | 57  | 52  | 49  | 48  |
| 10  | 67  | 57  | 50  | 46  | 66  | 56  | 50  | 46  | 55  | 50  | 46  |  | 55  | 49  | 46  |  | 54  | 49  | 46  | 44  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 114421 |
| 5°  | 113031 |
| 10° | 109773 |
| 15° | 105131 |
| 20° | 98475  |
| 25° | 89473  |
| 30° | 77278  |
| 35° | 61596  |
| 40° | 44855  |
| 45° | 29491  |
| 50° | 13816  |
| 55° | 4282   |
| 60° | 4122   |
| 65° | 3943   |
| 70° | 3783   |
| 75° | 3982   |
| 80° | 3662   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29491 cd/sqm

TEST NUMBER: P1284210

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1LI\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 48.4   | 8.2       |
| 10°-20°   | 129.6  | 21.9      |
| 20°-30°   | 168.4  | 28.5      |
| 30°-40°   | 142.9  | 24.2      |
| 40°-50°   | 73.7   | 12.5      |
| 50°-60°   | 14.2   | 2.4       |
| 60°-70°   | 7.7    | 1.3       |
| 70°-80°   | 4.7    | 0.8       |
| 80°-90°   | 1.4    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 346.4  | 58.6      |
| 0°-40°    | 489.3  | 82.8      |
| 0°-60°    | 577.2  | 97.7      |
| 0°-90°    | 591.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 591.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 522 |      |
| 5°  | 514 | 48   |
| 15° | 463 | 130  |
| 25° | 370 | 168  |
| 35° | 230 | 143  |
| 45° | 95  | 74   |
| 55° | 11  | 14   |
| 65° | 8   | 8    |
| 75° | 5   | 5    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1284210

CATALOG NUMBER: P3AS09R70B2750DE010 E3DL1LI\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 521.8 |
| 2.5°  | 520.0 |
| 5°    | 513.5 |
| 7.5°  | 504.2 |
| 10°   | 493.0 |
| 12.5° | 478.9 |
| 15°   | 463.1 |
| 17.5° | 443.7 |
| 20°   | 422.0 |
| 22.5° | 397.3 |
| 25°   | 369.8 |
| 27.5° | 338.6 |
| 30°   | 305.2 |
| 32.5° | 268.2 |
| 35°   | 230.1 |
| 37.5° | 192.5 |
| 40°   | 156.7 |
| 42.5° | 123.3 |
| 45°   | 95.1  |
| 47.5° | 69.8  |
| 50°   | 40.5  |
| 52.5° | 17.6  |
| 55°   | 11.2  |
| 57.5° | 10.6  |
| 60°   | 9.4   |
| 62.5° | 8.8   |
| 65°   | 7.6   |
| 67.5° | 7.0   |
| 70°   | 5.9   |
| 72.5° | 5.3   |
| 75°   | 4.7   |
| 77.5° | 3.5   |
| 80°   | 2.9   |
| 82.5° | 1.8   |
| 85°   | 1.2   |
| 87.5° | 0.6   |
| 90°   | 0.0   |

(END OF REPORT)