

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285192

Luminaire Tested: P3AS13R45B2750DE010 E3D1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3D1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1029.0 lumens
Efficiency: N/A
Efficacy: 53.9 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285192

CATALOG NUMBER: P3AS13R45B2750DE010 E3D1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285192

CATALOG NUMBER: P3AS13R45B2750DE010 E3D1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95	94	93	92	91	90	89	88
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93	92	91	90	89	88	87	86	85	84
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	90	89	88	87	86	85	84	83	82	81	80
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86	85	84	83	82	81	80	79	78	77	76	75
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82	81	80	79	78	77	76	75	74	73	72	71
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	78	77	76	75	74	73	72	71	70	69	68
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75	74	73	72	71	70	69	68	67	66	65	64
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72	71	70	69	68	67	66	65	64	63	62	61
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	68	67	66	65	64	63	62	61	60	59	58
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	65	64	63	62	61	60	59	58	57	56	55
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	63	62	61	60	59	58	57	56	55	54	53

AVERAGE LUMINANCE (cd/sqm):

0°	446127
5°	448513
10°	434728
15°	364293
20°	278484
25°	169534
30°	70542
35°	22593
40°	7042
45°	1427
50°	1058
55°	1185
60°	1009
65°	1193
70°	962
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1427 cd/sqm

TEST NUMBER: P1285192

CATALOG NUMBER: P3AS13R45B2750DE010 E3D1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.2	18.7
10°-20°	441.1	42.9
20°-30°	317.6	30.9
30°-40°	66.1	6.4
40°-50°	6.0	0.6
50°-60°	2.5	0.2
60°-70°	2.0	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.8	92.4
0°-40°	1016.9	98.8
0°-60°	1025.4	99.6
0°-90°	1029.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1029.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2034	
5°	2038	192
15°	1605	441
25°	701	318
35°	84	66
45°	5	6
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1285192

CATALOG NUMBER: P3AS13R45B2750DE010 E3D1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2034.5
2.5°	2035.3
5°	2037.6
7.5°	2023.0
10°	1952.4
12.5°	1805.0
15°	1604.7
17.5°	1399.8
20°	1193.4
22.5°	956.2
25°	700.7
27.5°	462.0
30°	278.6
32.5°	155.8
35°	84.4
37.5°	47.6
40°	24.6
42.5°	10.7
45°	4.6
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)