

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285197

Luminaire Tested: P3AS13R45B2750DE010 E3DL1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285197  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R45B2750DE010 E3DL1GPH\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 420.1 lumens  
Efficiency: N/A  
Efficacy: 22.0 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285197

CATALOG NUMBER: P3AS13R45B2750DE010 E3DL1GPH\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1285197

CATALOG NUMBER: P3AS13R45B2750DE010 E3DL1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |     |     |     | 0   |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 94  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 94  | 96  | 94  | 92  | 93  | 91  | 90  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 89  | 88  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 94  | 90  | 87  | 91  | 88  | 86  | 89  | 86  | 84  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  | 78  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  | 82  | 79  | 76  | 81  | 78  | 75  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  | 74  |
| 6   | 90  | 82  | 76  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  | 78  | 74  | 71  | 77  | 74  | 71  | 69  | 69  | 69  | 69  | 69  | 69  | 69  | 69  | 69  | 69  | 69  | 69  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  | 66  |
| 8   | 83  | 74  | 68  | 65  | 82  | 73  | 68  | 64  | 72  | 68  | 64  | 71  | 67  | 64  | 70  | 67  | 64  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  | 62  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 67  | 63  | 61  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  | 59  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 65  | 61  | 58  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  | 57  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 157729 |
| 5°  | 154039 |
| 10° | 141592 |
| 15° | 119978 |
| 20° | 93085  |
| 25° | 65060  |
| 30° | 40994  |
| 35° | 24119  |
| 40° | 13654  |
| 45° | 6636   |
| 50° | 2320   |
| 55° | 1873   |
| 60° | 1798   |
| 65° | 1764   |
| 70° | 1667   |
| 75° | 1610   |
| 80° | 1389   |
| 85° | 1006   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 6636 cd/sqm

TEST NUMBER: P1285197

CATALOG NUMBER: P3AS13R45B2750DE010 E3DL1GPH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 64.8   | 15.4      |
| 10°-20°   | 145.1  | 34.5      |
| 20°-30°   | 123.2  | 29.3      |
| 30°-40°   | 58.8   | 14.0      |
| 40°-50°   | 17.7   | 4.2       |
| 50°-60°   | 4.5    | 1.1       |
| 60°-70°   | 3.4    | 0.8       |
| 70°-80°   | 2.0    | 0.5       |
| 80°-90°   | 0.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 333.1  | 79.3      |
| 0°-40°    | 391.9  | 93.3      |
| 0°-60°    | 414.1  | 98.6      |
| 0°-90°    | 420.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 420.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 719 |      |
| 5°  | 700 | 65   |
| 15° | 528 | 145  |
| 25° | 269 | 123  |
| 35° | 90  | 59   |
| 45° | 21  | 18   |
| 55° | 5   | 4    |
| 65° | 3   | 3    |
| 75° | 2   | 2    |
| 85° | 0   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1285197

CATALOG NUMBER: P3AS13R45B2750DE010 E3DL1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 719.3 |
| 2.5°  | 714.8 |
| 5°    | 699.8 |
| 7.5°  | 673.8 |
| 10°   | 635.9 |
| 12.5° | 585.6 |
| 15°   | 528.5 |
| 17.5° | 465.0 |
| 20°   | 398.9 |
| 22.5° | 331.7 |
| 25°   | 268.9 |
| 27.5° | 211.8 |
| 30°   | 161.9 |
| 32.5° | 121.7 |
| 35°   | 90.1  |
| 37.5° | 66.5  |
| 40°   | 47.7  |
| 42.5° | 33.1  |
| 45°   | 21.4  |
| 47.5° | 12.0  |
| 50°   | 6.8   |
| 52.5° | 5.3   |
| 55°   | 4.9   |
| 57.5° | 4.5   |
| 60°   | 4.1   |
| 62.5° | 3.8   |
| 65°   | 3.4   |
| 67.5° | 3.0   |
| 70°   | 2.6   |
| 72.5° | 2.3   |
| 75°   | 1.9   |
| 77.5° | 1.5   |
| 80°   | 1.1   |
| 82.5° | 0.8   |
| 85°   | 0.4   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)