

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285200

Luminaire Tested: P3AS13R45B2750DE010 E3DL1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3DL1GPH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 422.0 lumens
Efficiency: N/A
Efficacy: 22.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285200

CATALOG NUMBER: P3AS13R45B2750DE010 E3DL1GPH_4000K

Luminous Intensity Polar Plot



CATALOG NUMBER: P3AS13R45B2750DE010 E3DL1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74			
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62			
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158474
5°	154765
10°	142260
15°	120546
20°	93528
25°	65375
30°	41196
35°	24253
40°	13711
45°	6667
50°	2320
55°	1873
60°	1842
65°	1764
70°	1667
75°	1610
80°	1389
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Luminance: 6667 cd/sqm

TEST NUMBER: P1285200

CATALOG NUMBER: P3AS13R45B2750DE010 E3DL1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.1	15.4
10°-20°	145.8	34.6
20°-30°	123.8	29.3
30°-40°	59.1	14.0
40°-50°	17.8	4.2
50°-60°	4.5	1.1
60°-70°	3.4	0.8
70°-80°	2.0	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.7	79.3
0°-40°	393.8	93.3
0°-60°	416.1	98.6
0°-90°	422.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	422.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	723	
5°	703	65
15°	531	146
25°	270	124
35°	91	59
45°	22	18
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1285200

CATALOG NUMBER: P3AS13R45B2750DE010 E3DL1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	722.7
2.5°	718.2
5°	703.1
7.5°	677.0
10°	638.9
12.5°	588.4
15°	531.0
17.5°	467.2
20°	400.8
22.5°	333.2
25°	270.2
27.5°	212.8
30°	162.7
32.5°	122.3
35°	90.6
37.5°	66.8
40°	47.9
42.5°	33.2
45°	21.5
47.5°	12.1
50°	6.8
52.5°	5.3
55°	4.9
57.5°	4.5
60°	4.2
62.5°	3.8
65°	3.4
67.5°	3.0
70°	2.6
72.5°	2.3
75°	1.9
77.5°	1.5
80°	1.1
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)