

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284248

Luminaire Tested: P3AS09R70B2750DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70B2750DE010 E3DLP1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 581.0 lumens
Efficiency: N/A
Efficacy: 44.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284248

CATALOG NUMBER: P3AS09R70B2750DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284248

CATALOG NUMBER: P3AS09R70B2750DE010 E3DLP1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112469
5°	111138
10°	107925
15°	103338
20°	96795
25°	87949
30°	75961
35°	60552
40°	44111
45°	28995
50°	13577
55°	4205
60°	4035
65°	3891
70°	3719
75°	3897
80°	3662
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28995 cd/sqm

TEST NUMBER: P1284248

CATALOG NUMBER: P3AS09R70B2750DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.5	8.2
10°-20°	127.4	21.9
20°-30°	165.6	28.5
30°-40°	140.5	24.2
40°-50°	72.5	12.5
50°-60°	14.0	2.4
60°-70°	7.6	1.3
70°-80°	4.7	0.8
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.5	58.6
0°-40°	481.0	82.8
0°-60°	567.5	97.7
0°-90°	581.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	581.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	513	
5°	505	48
15°	455	127
25°	364	166
35°	226	141
45°	94	72
55°	11	14
65°	8	8
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1284248

CATALOG NUMBER: P3AS09R70B2750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	512.9
2.5°	511.2
5°	504.9
7.5°	495.6
10°	484.7
12.5°	470.8
15°	455.2
17.5°	436.2
20°	414.8
22.5°	390.6
25°	363.5
27.5°	332.9
30°	300.0
32.5°	263.7
35°	226.2
37.5°	189.2
40°	154.1
42.5°	121.2
45°	93.5
47.5°	68.7
50°	39.8
52.5°	17.3
55°	11.0
57.5°	10.4
60°	9.2
62.5°	8.7
65°	7.5
67.5°	6.9
70°	5.8
72.5°	5.2
75°	4.6
77.5°	3.5
80°	2.9
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)