

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285229

Luminaire Tested: P3AS13R45B2750DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285229
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 80CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 330.0 lumens
Efficiency: N/A
Efficacy: 17.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285229

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1285229

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93		91			
2	106	100	95	91		103	98	94	90		95	91	88		92	89	86		89	87	85		83			
3	99	92	86	82		97	91	85	81		88	83	80		85	81	78		83	80	77		75			
4	94	85	78	74		92	84	78	73		81	76	72		79	75	71		77	74	71		69			
5	88	79	72	67		86	78	71	67		76	70	66		74	69	65		72	68	65		63			
6	83	73	66	61		81	72	66	61		71	65	61		69	64	60		68	63	60		58			
7	78	68	61	57		77	67	61	56		66	60	56		65	60	56		64	59	55		54			
8	74	64	57	52		73	63	57	52		62	56	52		61	56	52		60	55	52		50			
9	70	60	53	49		69	59	53	49		58	52	48		57	52	48		56	52	48		47			
10	67	56	50	45		66	56	49	45		55	49	45		54	49	45		53	48	45		44			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69972
5°	68721
10°	65040
15°	59319
20°	52458
25°	45559
30°	39095
35°	32578
40°	24274
45°	14854
50°	6891
55°	5390
60°	5175
65°	4722
70°	4360
75°	4151
80°	3788
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14854 cd/sqm

TEST NUMBER: P1285229

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.2	8.8
10°-20°	72.7	22.0
20°-30°	86.4	26.2
30°-40°	75.1	22.8
40°-50°	37.7	11.4
50°-60°	13.1	4.0
60°-70°	9.1	2.8
70°-80°	5.1	1.5
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	188.3	57.1
0°-40°	263.4	79.8
0°-60°	314.2	95.2
0°-90°	330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	319	
5°	312	29
15°	261	73
25°	188	86
35°	122	75
45°	48	38
55°	14	13
65°	9	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1285229

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	319.1
2.5°	317.6
5°	312.2
7.5°	303.9
10°	292.1
12.5°	277.6
15°	261.3
17.5°	243.0
20°	224.8
22.5°	206.1
25°	188.3
27.5°	171.1
30°	154.4
32.5°	138.4
35°	121.7
37.5°	103.8
40°	84.8
42.5°	66.2
45°	47.9
47.5°	31.6
50°	20.2
52.5°	15.6
55°	14.1
57.5°	12.9
60°	11.8
62.5°	10.6
65°	9.1
67.5°	8.0
70°	6.8
72.5°	5.7
75°	4.9
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.1
87.5°	0.8
90°	0.0

(END OF REPORT)