

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285247

Luminaire Tested: P3AS13R45B2750DE010 E3DLD1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3DLD1WH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 666.0 lumens
Efficiency: N/A
Efficacy: 34.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285247

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1WH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285247

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83	80	77	75
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77	74	71	69
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72	68	65	63
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64	59	55	54
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60	55	52	50
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56	52	48	47
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53	48	45	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141217
5°	138697
10°	131260
15°	119706
20°	105849
25°	91917
30°	78898
35°	65745
40°	49006
45°	29988
50°	13884
55°	10857
60°	10438
65°	9547
70°	8848
75°	8472
80°	7703
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29988 cd/sqm

TEST NUMBER: P1285247

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	8.8
10°-20°	146.8	22.0
20°-30°	174.4	26.2
30°-40°	151.5	22.8
40°-50°	76.0	11.4
50°-60°	26.4	4.0
60°-70°	18.5	2.8
70°-80°	10.3	1.6
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.1	57.1
0°-40°	531.6	79.8
0°-60°	634.0	95.2
0°-90°	666.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	644	
5°	630	59
15°	527	147
25°	380	174
35°	246	152
45°	97	76
55°	28	26
65°	18	18
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1285247

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLD1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	644.0
2.5°	640.9
5°	630.1
7.5°	613.3
10°	589.5
12.5°	560.3
15°	527.3
17.5°	490.4
20°	453.6
22.5°	416.0
25°	379.9
27.5°	345.4
30°	311.6
32.5°	279.4
35°	245.6
37.5°	209.5
40°	171.2
42.5°	133.5
45°	96.7
47.5°	63.7
50°	40.7
52.5°	31.5
55°	28.4
57.5°	26.1
60°	23.8
62.5°	21.5
65°	18.4
67.5°	16.1
70°	13.8
72.5°	11.5
75°	10.0
77.5°	7.7
80°	6.1
82.5°	4.6
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)