

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284288

Luminaire Tested: P3AS13R15B2750DE010 E3CD1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15B2750DE010 E3CD1MMS_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 957.0 lumens
Efficiency: N/A
Efficacy: 50.1 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284288

CATALOG NUMBER: P3AS13R15B2750DE010 E3CD1MMS_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284288

CATALOG NUMBER: P3AS13R15B2750DE010 E3CD1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101	100	100		98
2	113	110	107	105	111	108	106	104	105	103	101		102	101	99		99	98	97		96
3	110	106	103	100	108	105	102	100	102	100	98		100	98	97		98	97	95		94
4	107	103	100	97	106	102	99	97	100	97	95		98	96	94		97	95	93		92
5	105	100	97	94	104	99	96	94	98	95	93		96	94	92		95	93	92		91
6	103	98	94	92	102	97	94	92	96	93	91		95	92	91		94	92	90		89
7	101	96	92	90	100	95	92	90	94	91	89		93	91	89		92	90	89		88
8	99	94	90	88	98	93	90	88	92	90	88		92	89	87		91	89	87		86
9	97	92	89	87	97	92	89	86	91	88	86		90	88	86		90	87	86		85
10	96	90	87	85	95	90	87	85	89	87	85		89	86	85		88	86	85		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1860180
5°	1559010
10°	734366
15°	221409
20°	81930
25°	31841
30°	11875
35°	3641
40°	1288
45°	713
50°	512
55°	573
60°	658
65°	415
70°	513
75°	678
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1284288

CATALOG NUMBER: P3AS13R15B2750DE010 E3CD1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	547.6	57.2
10°-20°	325.5	34.0
20°-30°	68.4	7.1
30°-40°	11.0	1.2
40°-50°	1.9	0.2
50°-60°	1.3	0.1
60°-70°	0.9	0.1
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	941.4	98.4
0°-40°	952.4	99.5
0°-60°	955.6	99.9
0°-90°	957.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	957.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8483	
5°	7083	548
15°	975	325
25°	132	68
35°	14	11
45°	2	2
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1284288

CATALOG NUMBER: P3AS13R15B2750DE010 E3CD1MMS_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	8483.1
1°	8456.6
2°	8321.9
3°	8052.6
4°	7657.6
5°	7082.6
6°	6407.0
7°	5634.5
8°	4896.8
9°	4061.5
10°	3298.1
12.5°	1779.5
15°	975.3
17.5°	571.2
20°	351.1
22.5°	214.9
25°	131.6
27.5°	79.4
30°	46.9
32.5°	26.5
35°	13.6
37.5°	7.6
40°	4.5
42.5°	3.0
45°	2.3
47.5°	1.5
50°	1.5
52.5°	1.5
55°	1.5
57.5°	1.5
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)