

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284340

Luminaire Tested: P3AS13R15B2750DE010 E3DL1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15B2750DE010 E3DL1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 798.0 lumens
Efficiency: N/A
Efficacy: 41.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284340

CATALOG NUMBER: P3AS13R15B2750DE010 E3DL1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284340

CATALOG NUMBER: P3AS13R15B2750DE010 E3DL1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	681700
5°	605105
10°	420233
15°	248514
20°	141529
25°	80908
30°	44766
35°	23878
40°	13196
45°	7164
50°	4469
55°	3517
60°	3026
65°	2802
70°	2436
75°	2626
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7164 cd/sqm

TEST NUMBER: P1284340

CATALOG NUMBER: P3AS13R15B2750DE010 E3DL1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.8	29.3
10°-20°	308.5	38.7
20°-30°	158.8	19.9
30°-40°	59.6	7.5
40°-50°	19.5	2.4
50°-60°	8.4	1.1
60°-70°	5.3	0.7
70°-80°	3.1	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.1	87.9
0°-40°	760.8	95.3
0°-60°	788.7	98.8
0°-90°	798.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	798.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3109	
5°	2749	234
15°	1095	309
25°	334	159
35°	89	60
45°	23	20
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1284340

CATALOG NUMBER: P3AS13R15B2750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3108.8
1°	3102.7
2°	3061.9
3°	2984.3
4°	2882.0
5°	2749.0
6°	2598.4
7°	2433.1
8°	2249.4
9°	2067.9
10°	1887.3
12.5°	1452.2
15°	1094.7
17.5°	819.5
20°	606.5
22.5°	452.8
25°	334.4
27.5°	243.7
30°	176.8
32.5°	125.3
35°	89.2
37.5°	63.8
40°	46.1
42.5°	33.1
45°	23.1
47.5°	16.9
50°	13.1
52.5°	10.8
55°	9.2
57.5°	7.7
60°	6.9
62.5°	6.1
65°	5.4
67.5°	4.6
70°	3.8
72.5°	3.8
75°	3.1
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)