

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285275

Luminaire Tested: P3AS13R45B2750DE010 E3DLP1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285275
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3DLP1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 80CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 555.0 lumens
Efficiency: N/A
Efficacy: 29.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285275

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285275

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165316
5°	161545
10°	149029
15°	129581
20°	106456
25°	82819
30°	61174
35°	43045
40°	26879
45°	14544
50°	7880
55°	6767
60°	6052
65°	5189
70°	4424
75°	4575
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14544 cd/sqm

TEST NUMBER: P1285275

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.0	12.2
10°-20°	157.8	28.4
20°-30°	156.6	28.2
30°-40°	100.9	18.2
40°-50°	38.9	7.0
50°-60°	15.8	2.8
60°-70°	10.0	1.8
70°-80°	5.4	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	382.4	68.9
0°-40°	483.3	87.1
0°-60°	538.0	96.9
0°-90°	555.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	555.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	754	
5°	734	68
15°	571	158
25°	342	157
35°	161	101
45°	47	39
55°	18	16
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1285275

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	753.9
2.5°	750.0
5°	733.9
7.5°	706.2
10°	669.3
12.5°	623.1
15°	570.8
17.5°	513.9
20°	456.2
22.5°	397.7
25°	342.3
27.5°	290.0
30°	241.6
32.5°	199.2
35°	160.8
37.5°	126.2
40°	93.9
42.5°	67.7
45°	46.9
47.5°	31.5
50°	23.1
52.5°	19.2
55°	17.7
57.5°	15.4
60°	13.8
62.5°	11.5
65°	10.0
67.5°	8.5
70°	6.9
72.5°	6.2
75°	5.4
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)