

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285281

Luminaire Tested: P3AS13R45B2750DE010 E3DLP1WH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285281
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45B2750DE010 E3DLP1WH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 80CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 918.0 lumens
Efficiency: N/A
Efficacy: 48.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285281

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285281

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	96	96	96	96	96	96	96	96	96	96	96	94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	89	89	89	89	89	89	89	89	89	89	89	88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83	83	83	83	83	83	83	83	83	83	83	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78	78	78	78	78	78	78	78	78	78	78	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74	74	74	74	74	74	74	74	74	74	74	74
6	90	82	77	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70	70	70	70	70	70	70	70	70	70	70	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66	66	66	66	66	66	66	66	66	66	66	66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62	62	62	62	62	62	62	62	62	62	62	62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59	59	59	59	59	59	59	59	59	59	59	59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57	57	57	57	57	57	57	57	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	344731
5°	336671
10°	309480
15°	262226
20°	203461
25°	142218
30°	89583
35°	52735
40°	29856
45°	14513
50°	5049
55°	4091
60°	3947
65°	3840
70°	3654
75°	3474
80°	3157
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 14513 cd/sqm

TEST NUMBER: P1285281

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.6	15.4
10°-20°	317.2	34.6
20°-30°	269.3	29.3
30°-40°	128.5	14.0
40°-50°	38.7	4.2
50°-60°	9.8	1.1
60°-70°	7.3	0.8
70°-80°	4.3	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	728.1	79.3
0°-40°	856.6	93.3
0°-60°	905.1	98.6
0°-90°	918.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	918.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1572	
5°	1530	142
15°	1155	317
25°	588	269
35°	197	128
45°	47	39
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1285281

CATALOG NUMBER: P3AS13R45B2750DE010 E3DLP1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1572.1
2.5°	1562.3
5°	1529.5
7.5°	1472.8
10°	1389.9
12.5°	1279.9
15°	1155.1
17.5°	1016.4
20°	871.9
22.5°	724.9
25°	587.8
27.5°	463.0
30°	353.8
32.5°	266.0
35°	197.0
37.5°	145.3
40°	104.3
42.5°	72.2
45°	46.8
47.5°	26.3
50°	14.8
52.5°	11.5
55°	10.7
57.5°	9.9
60°	9.0
62.5°	8.2
65°	7.4
67.5°	6.6
70°	5.7
72.5°	4.9
75°	4.1
77.5°	3.3
80°	2.5
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)