

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284367

Luminaire Tested: P3AS13R15B2750DE010 E3DLD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15B2750DE010 E3DLD1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 606.0 lumens
Efficiency: N/A
Efficacy: 31.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284367
CATALOG NUMBER: P3AS13R15B2750DE010 E3DLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1284367
 CATALOG NUMBER: P3AS13R15B2750DE010 E3DLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152861
5°	148712
10°	135891
15°	119025
20°	102116
25°	85263
30°	68238
35°	51183
40°	37127
45°	24282
50°	15181
55°	10284
60°	9078
65°	8354
70°	7886
75°	7117
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24282 cd/sqm



TEST NUMBER: P1284367

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.3	10.3
10°-20°	146.1	24.1
20°-30°	161.0	26.6
30°-40°	120.6	19.9
40°-50°	62.5	10.3
50°-60°	25.9	4.3
60°-70°	16.0	2.6
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.4	61.0
0°-40°	490.0	80.9
0°-60°	578.3	95.4
0°-90°	606.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	697	
5°	676	62
15°	524	146
25°	352	161
35°	191	121
45°	78	62
55°	27	26
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1284367
CATALOG NUMBER: P3AS13R15B2750DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	697.1
1°	697.8
2°	695.5
3°	690.9
4°	684.0
5°	675.6
6°	664.8
7°	653.3
8°	639.5
9°	624.9
10°	610.3
12.5°	568.1
15°	524.3
17.5°	480.6
20°	437.6
22.5°	393.8
25°	352.4
27.5°	310.9
30°	269.5
32.5°	228.8
35°	191.2
37.5°	158.9
40°	129.7
42.5°	102.9
45°	78.3
47.5°	59.1
50°	44.5
52.5°	33.0
55°	26.9
57.5°	23.8
60°	20.7
62.5°	18.4
65°	16.1
67.5°	13.8
70°	12.3
72.5°	10.0
75°	8.4
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)