

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284380

Luminaire Tested: P3AS13R15B2750DE010 E3DLD1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284380
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15B2750DE010 E3DLD1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 607.0 lumens
Efficiency: N/A
Efficacy: 31.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284380

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLD1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284380

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLD1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153102
5°	148954
10°	136114
15°	119229
20°	102279
25°	85408
30°	68340
35°	51263
40°	37213
45°	24313
50°	15215
55°	10284
60°	9122
65°	8354
70°	7886
75°	7202
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24313 cd/sqm

TEST NUMBER: P1284380

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLD1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	10.3
10°-20°	146.3	24.1
20°-30°	161.2	26.6
30°-40°	120.8	19.9
40°-50°	62.6	10.3
50°-60°	25.9	4.3
60°-70°	16.1	2.6
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.0	61.0
0°-40°	490.8	80.9
0°-60°	579.3	95.4
0°-90°	607.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	607.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	698	
5°	677	62
15°	525	146
25°	353	161
35°	192	121
45°	78	63
55°	27	26
65°	16	16
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1284380

CATALOG NUMBER: P3AS13R15B2750DE010 E3DLD1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	698.2
1°	699.0
2°	696.7
3°	692.1
4°	685.2
5°	676.7
6°	665.9
7°	654.4
8°	640.6
9°	625.9
10°	611.3
12.5°	569.0
15°	525.2
17.5°	481.4
20°	438.3
22.5°	394.5
25°	353.0
27.5°	311.4
30°	269.9
32.5°	229.2
35°	191.5
37.5°	159.2
40°	130.0
42.5°	103.0
45°	78.4
47.5°	59.2
50°	44.6
52.5°	33.1
55°	26.9
57.5°	23.8
60°	20.8
62.5°	18.5
65°	16.1
67.5°	13.8
70°	12.3
72.5°	10.0
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)