

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285348

Luminaire Tested: P3AS13R50B2750DE010 E3DL1H\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285348  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R50B2750DE010 E3DL1H\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 851.0 lumens  
Efficiency: N/A  
Efficacy: 44.6 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285348

CATALOG NUMBER: P3AS13R50B2750DE010 E3DL1H\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1285348

CATALOG NUMBER: P3AS13R50B2750DE010 E3DL1H\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  |  | 95  | 93  | 91  |  | 93  |
| 3   | 103 | 97  | 92  | 88  | 101 | 95  | 91  | 87  | 93  | 89  | 86  |  | 90  | 87  | 84  |  | 88  |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  | 87  | 83  | 80  |  | 85  | 82  | 79  |  | 84  |
| 5   | 93  | 85  | 80  | 75  | 92  | 84  | 79  | 75  | 83  | 78  | 74  |  | 81  | 77  | 74  |  | 79  |
| 6   | 89  | 80  | 75  | 71  | 88  | 80  | 74  | 70  | 78  | 73  | 70  |  | 77  | 73  | 69  |  | 75  |
| 7   | 85  | 76  | 70  | 66  | 84  | 75  | 70  | 66  | 74  | 69  | 66  |  | 73  | 69  | 65  |  | 72  |
| 8   | 81  | 72  | 66  | 62  | 80  | 71  | 66  | 62  | 70  | 65  | 62  |  | 69  | 65  | 62  |  | 68  |
| 9   | 78  | 68  | 63  | 59  | 76  | 68  | 62  | 59  | 67  | 62  | 59  |  | 66  | 62  | 58  |  | 65  |
| 10  | 74  | 65  | 59  | 56  | 73  | 65  | 59  | 56  | 64  | 59  | 55  |  | 63  | 58  | 55  |  | 62  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 270943 |
| 5°  | 265485 |
| 10° | 248671 |
| 15° | 222612 |
| 20° | 187336 |
| 25° | 142968 |
| 30° | 92926  |
| 35° | 55091  |
| 40° | 31831  |
| 45° | 15971  |
| 50° | 5936   |
| 55° | 4626   |
| 60° | 4298   |
| 65° | 3943   |
| 70° | 3911   |
| 75° | 3813   |
| 80° | 3788   |
| 85° | 3774   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15971 cd/sqm

TEST NUMBER: P1285348

CATALOG NUMBER: P3AS13R50B2750DE010 E3DL1H\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 112.2  | 13.2      |
| 10°-20°   | 271.2  | 31.9      |
| 20°-30°   | 266.0  | 31.3      |
| 30°-40°   | 134.0  | 15.7      |
| 40°-50°   | 42.4   | 5.0       |
| 50°-60°   | 11.0   | 1.3       |
| 60°-70°   | 7.8    | 0.9       |
| 70°-80°   | 4.8    | 0.6       |
| 80°-90°   | 1.7    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 649.4  | 76.3      |
| 0°-40°    | 783.5  | 92.1      |
| 0°-60°    | 836.8  | 98.3      |
| 0°-90°    | 851.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 851.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1236 |      |
| 5°  | 1206 | 112  |
| 15° | 981  | 271  |
| 25° | 591  | 266  |
| 35° | 206  | 134  |
| 45° | 52   | 42   |
| 55° | 12   | 11   |
| 65° | 8    | 8    |
| 75° | 4    | 5    |
| 85° | 2    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1285348

CATALOG NUMBER: P3AS13R50B2750DE010 E3DL1H\_3000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1235.6 |
| 2.5°  | 1228.0 |
| 5°    | 1206.1 |
| 7.5°  | 1166.7 |
| 10°   | 1116.8 |
| 12.5° | 1052.5 |
| 15°   | 980.6  |
| 17.5° | 897.4  |
| 20°   | 802.8  |
| 22.5° | 700.7  |
| 25°   | 590.9  |
| 27.5° | 474.4  |
| 30°   | 367.0  |
| 32.5° | 276.2  |
| 35°   | 205.8  |
| 37.5° | 152.1  |
| 40°   | 111.2  |
| 42.5° | 78.7   |
| 45°   | 51.5   |
| 47.5° | 29.5   |
| 50°   | 17.4   |
| 52.5° | 12.9   |
| 55°   | 12.1   |
| 57.5° | 10.6   |
| 60°   | 9.8    |
| 62.5° | 9.1    |
| 65°   | 7.6    |
| 67.5° | 6.8    |
| 70°   | 6.1    |
| 72.5° | 5.3    |
| 75°   | 4.5    |
| 77.5° | 3.8    |
| 80°   | 3.0    |
| 82.5° | 2.3    |
| 85°   | 1.5    |
| 87.5° | 0.8    |
| 90°   | 0.0    |

(END OF REPORT)