

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285390

Luminaire Tested: P3AS13R50B2750DE010 E3DLD1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50B2750DE010 E3DLD1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 674.0 lumens
Efficiency: N/A
Efficacy: 35.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285390

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285390

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136963
5°	134955
10°	128967
15°	119456
20°	107343
25°	94360
30°	80240
35°	65076
40°	48892
45°	31476
50°	14942
55°	11775
60°	11139
65°	10377
70°	9361
75°	8472
80°	7829
85°	7799

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31476 cd/sqm

TEST NUMBER: P1285390

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	8.5
10°-20°	146.7	21.8
20°-30°	178.2	26.4
30°-40°	151.2	22.4
40°-50°	78.5	11.6
50°-60°	28.3	4.2
60°-70°	19.6	2.9
70°-80°	10.7	1.6
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	382.4	56.7
0°-40°	533.6	79.2
0°-60°	640.4	95.0
0°-90°	674.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	674.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	625	
5°	613	57
15°	526	147
25°	390	178
35°	243	151
45°	102	79
55°	31	28
65°	20	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1285390

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	624.6
2.5°	622.3
5°	613.1
7.5°	599.2
10°	579.2
12.5°	553.9
15°	526.2
17.5°	494.6
20°	460.0
22.5°	424.6
25°	390.0
27.5°	353.9
30°	316.9
32.5°	280.0
35°	243.1
37.5°	206.9
40°	170.8
42.5°	136.2
45°	101.5
47.5°	67.7
50°	43.8
52.5°	33.8
55°	30.8
57.5°	27.7
60°	25.4
62.5°	22.3
65°	20.0
67.5°	16.9
70°	14.6
72.5°	12.3
75°	10.0
77.5°	7.7
80°	6.2
82.5°	4.6
85°	3.1
87.5°	1.5
90°	0.0

(END OF REPORT)