

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284417

Luminaire Tested: P3AS13R15B2750DE010 E3PHLD1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284417
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R15B2750DE010 E3PHLD1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 506.0 lumens
Efficiency: N/A
Efficacy: 26.5 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284417

CATALOG NUMBER: P3AS13R15B2750DE010 E3PHLD1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1284417

CATALOG NUMBER: P3AS13R15B2750DE010 E3PHLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	71	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	47	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147247
5°	138036
10°	113180
15°	87946
20°	69423
25°	55310
30°	44412
35°	36246
40°	29856
45°	25119
50°	21594
55°	18656
60°	16534
65°	14372
70°	12823
75°	10336
80°	8461
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 25119 cd/sqm

TEST NUMBER: P1284417

CATALOG NUMBER: P3AS13R15B2750DE010 E3PHLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.0	11.1
10°-20°	108.5	21.4
20°-30°	105.5	20.8
30°-40°	85.2	16.8
40°-50°	63.3	12.5
50°-60°	44.2	8.7
60°-70°	27.7	5.5
70°-80°	13.2	2.6
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.0	53.4
0°-40°	355.2	70.2
0°-60°	462.7	91.5
0°-90°	506.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	506.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	672	
5°	627	56
15°	387	109
25°	229	105
35°	135	85
45°	81	63
55°	49	44
65°	28	28
75°	12	13
85°	2	2
90°	0	

TEST NUMBER: P1284417

CATALOG NUMBER: P3AS13R15B2750DE010 E3PHLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	671.5
2.5°	660.4
5°	627.1
7.5°	573.8
10°	508.3
12.5°	444.0
15°	387.4
17.5°	339.6
20°	297.5
22.5°	260.8
25°	228.6
27.5°	199.8
30°	175.4
32.5°	154.3
35°	135.4
37.5°	118.8
40°	104.3
42.5°	92.1
45°	81.0
47.5°	72.1
50°	63.3
52.5°	55.5
55°	48.8
57.5°	43.3
60°	37.7
62.5°	32.2
65°	27.7
67.5°	23.3
70°	20.0
72.5°	15.5
75°	12.2
77.5°	8.9
80°	6.7
82.5°	3.3
85°	2.2
87.5°	0.0
90°	0.0

(END OF REPORT)