

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285395

Luminaire Tested: P3AS13R50B2750DE010 E3DLD1WH\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285395  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R50B2750DE010 E3DLD1WH\_4000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 674.0 lumens  
Efficiency: N/A  
Efficacy: 35.3 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285395

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1WH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1285395

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 99  |  | 99  | 97  | 96  |  | 95  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 89  |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  |  | 85  | 81  | 78  |  | 83  |
| 4   | 93  | 85  | 78  | 73  | 91  | 83  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 5   | 88  | 78  | 72  | 67  | 86  | 77  | 71  | 66  | 75  | 70  | 66  |  | 74  | 69  | 65  |  | 72  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 65  | 61  | 70  | 65  | 60  |  | 69  | 64  | 60  |  | 67  |
| 7   | 78  | 68  | 61  | 56  | 77  | 67  | 61  | 56  | 66  | 60  | 56  |  | 64  | 59  | 55  |  | 63  |
| 8   | 74  | 63  | 57  | 52  | 73  | 63  | 56  | 52  | 61  | 56  | 52  |  | 60  | 55  | 51  |  | 59  |
| 9   | 70  | 59  | 53  | 48  | 69  | 59  | 52  | 48  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 56  |
| 10  | 66  | 56  | 49  | 45  | 65  | 55  | 49  | 45  | 54  | 49  | 45  |  | 54  | 48  | 45  |  | 53  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 136963 |
| 5°  | 134955 |
| 10° | 128967 |
| 15° | 119456 |
| 20° | 107343 |
| 25° | 94360  |
| 30° | 80240  |
| 35° | 65076  |
| 40° | 48892  |
| 45° | 31476  |
| 50° | 14942  |
| 55° | 11775  |
| 60° | 11139  |
| 65° | 10377  |
| 70° | 9361   |
| 75° | 8472   |
| 80° | 7829   |
| 85° | 7799   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31476 cd/sqm

TEST NUMBER: P1285395

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1WH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 57.5   | 8.5       |
| 10°-20°   | 146.7  | 21.8      |
| 20°-30°   | 178.2  | 26.4      |
| 30°-40°   | 151.2  | 22.4      |
| 40°-50°   | 78.5   | 11.6      |
| 50°-60°   | 28.3   | 4.2       |
| 60°-70°   | 19.6   | 2.9       |
| 70°-80°   | 10.7   | 1.6       |
| 80°-90°   | 3.3    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 382.4  | 56.7      |
| 0°-40°    | 533.6  | 79.2      |
| 0°-60°    | 640.4  | 95.0      |
| 0°-90°    | 674.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 674.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 625 |      |
| 5°  | 613 | 57   |
| 15° | 526 | 147  |
| 25° | 390 | 178  |
| 35° | 243 | 151  |
| 45° | 102 | 79   |
| 55° | 31  | 28   |
| 65° | 20  | 20   |
| 75° | 10  | 11   |
| 85° | 3   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1285395

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLD1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 624.6 |
| 2.5°  | 622.3 |
| 5°    | 613.1 |
| 7.5°  | 599.2 |
| 10°   | 579.2 |
| 12.5° | 553.9 |
| 15°   | 526.2 |
| 17.5° | 494.6 |
| 20°   | 460.0 |
| 22.5° | 424.6 |
| 25°   | 390.0 |
| 27.5° | 353.9 |
| 30°   | 316.9 |
| 32.5° | 280.0 |
| 35°   | 243.1 |
| 37.5° | 206.9 |
| 40°   | 170.8 |
| 42.5° | 136.2 |
| 45°   | 101.5 |
| 47.5° | 67.7  |
| 50°   | 43.8  |
| 52.5° | 33.8  |
| 55°   | 30.8  |
| 57.5° | 27.7  |
| 60°   | 25.4  |
| 62.5° | 22.3  |
| 65°   | 20.0  |
| 67.5° | 16.9  |
| 70°   | 14.6  |
| 72.5° | 12.3  |
| 75°   | 10.0  |
| 77.5° | 7.7   |
| 80°   | 6.2   |
| 82.5° | 4.6   |
| 85°   | 3.1   |
| 87.5° | 1.5   |
| 90°   | 0.0   |

(END OF REPORT)