

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285422

Luminaire Tested: P3AS13R50B2750DE010 E3DLP1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285422
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50B2750DE010 E3DLP1WH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 863.0 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285422

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1WH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285422

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95		94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89		87
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88	85	83		82
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84	80	78		76
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79	76	73		72
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75	72	69		67
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72	68	65		64
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68	64	61		60
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65	61	58		57
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62	58	55		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	274759
5°	269227
10°	252189
15°	225745
20°	189973
25°	145000
30°	94217
35°	55867
40°	32289
45°	16188
50°	6004
55°	4702
60°	4386
65°	3995
70°	3911
75°	3897
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16188 cd/sqm

TEST NUMBER: P1285422

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.8	13.2
10°-20°	275.0	31.9
20°-30°	269.8	31.3
30°-40°	135.9	15.8
40°-50°	42.9	5.0
50°-60°	11.1	1.3
60°-70°	7.9	0.9
70°-80°	4.9	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	658.6	76.3
0°-40°	794.5	92.1
0°-60°	848.6	98.3
0°-90°	863.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	863.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1253	
5°	1223	114
15°	994	275
25°	599	270
35°	209	136
45°	52	43
55°	12	11
65°	8	8
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1285422

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1253.0
2.5°	1245.3
5°	1223.1
7.5°	1183.2
10°	1132.6
12.5°	1067.3
15°	994.4
17.5°	910.0
20°	814.1
22.5°	710.5
25°	599.3
27.5°	481.1
30°	372.1
32.5°	280.1
35°	208.7
37.5°	154.2
40°	112.8
42.5°	79.8
45°	52.2
47.5°	29.9
50°	17.6
52.5°	13.0
55°	12.3
57.5°	10.7
60°	10.0
62.5°	9.2
65°	7.7
67.5°	6.9
70°	6.1
72.5°	5.4
75°	4.6
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)