

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285423

Luminaire Tested: P3AS13R50B2750DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50B2750DE010 E3DLP1WH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 851.0 lumens
Efficiency: N/A
Efficacy: 44.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285423

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285423

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	270943
5°	265485
10°	248671
15°	222612
20°	187336
25°	142968
30°	92926
35°	55091
40°	31831
45°	15971
50°	5936
55°	4626
60°	4298
65°	3943
70°	3911
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15971 cd/sqm

TEST NUMBER: P1285423

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.2	13.2
10°-20°	271.2	31.9
20°-30°	266.0	31.3
30°-40°	134.0	15.7
40°-50°	42.4	5.0
50°-60°	11.0	1.3
60°-70°	7.8	0.9
70°-80°	4.8	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	649.4	76.3
0°-40°	783.5	92.1
0°-60°	836.8	98.3
0°-90°	851.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	851.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1236	
5°	1206	112
15°	981	271
25°	591	266
35°	206	134
45°	52	42
55°	12	11
65°	8	8
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1285423

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1235.6
2.5°	1228.0
5°	1206.1
7.5°	1166.7
10°	1116.8
12.5°	1052.5
15°	980.6
17.5°	897.4
20°	802.8
22.5°	700.7
25°	590.9
27.5°	474.4
30°	367.0
32.5°	276.2
35°	205.8
37.5°	152.1
40°	111.2
42.5°	78.7
45°	51.5
47.5°	29.5
50°	17.4
52.5°	12.9
55°	12.1
57.5°	10.6
60°	9.8
62.5°	9.1
65°	7.6
67.5°	6.8
70°	6.1
72.5°	5.3
75°	4.5
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)