

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285452

Luminaire Tested: P3AS13R55B2750DE010 E3CD1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285452
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3CD1MMS_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1021.0 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285452

CATALOG NUMBER: P3AS13R55B2750DE010 E3CD1MMS_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285452

CATALOG NUMBER: P3AS13R55B2750DE010 E3CD1MMS_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96		94
2	109	104	101	98	107	103	99	96	100	97	94		97	94	92		94	92	90		89
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90	87	85		84
4	99	92	87	84	98	91	87	83	89	85	82		87	84	81		85	83	80		79
5	95	87	82	78	93	86	81	78	85	80	77		83	79	76		82	78	76		74
6	91	83	77	73	89	82	77	73	80	76	72		79	75	72		78	74	72		70
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74	70	68		66
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71	67	64		63
9	79	71	65	61	78	70	65	61	69	64	61		68	64	61		68	64	61		60
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	283179
5°	280541
10°	291823
15°	287766
20°	265370
25°	215916
30°	131134
35°	45401
40°	12967
45°	6202
50°	2627
55°	1185
60°	1360
65°	1193
70°	962
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6202 cd/sqm

TEST NUMBER: P1285452

CATALOG NUMBER: P3AS13R55B2750DE010 E3CD1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.2	12.1
10°-20°	352.3	34.5
20°-30°	392.8	38.5
30°-40°	128.5	12.6
40°-50°	17.0	1.7
50°-60°	3.6	0.4
60°-70°	2.1	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	868.3	85.0
0°-40°	996.8	97.6
0°-60°	1017.3	99.6
0°-90°	1021.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1021.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1291	
5°	1274	123
15°	1268	352
25°	892	393
35°	170	128
45°	20	17
55°	3	4
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1285452

CATALOG NUMBER: P3AS13R55B2750DE010 E3CD1MMS_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1291.4
2.5°	1282.2
5°	1274.5
7.5°	1292.9
10°	1310.6
12.5°	1301.4
15°	1267.6
17.5°	1213.9
20°	1137.2
22.5°	1031.3
25°	892.4
27.5°	715.9
30°	517.9
32.5°	317.7
35°	169.6
37.5°	85.9
40°	45.3
42.5°	29.2
45°	20.0
47.5°	13.8
50°	7.7
52.5°	4.6
55°	3.1
57.5°	3.1
60°	3.1
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)