

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285506

Luminaire Tested: P3AS13R55B2750DE010 E3DL1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DL1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 895.0 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285506

CATALOG NUMBER: P3AS13R55B2750DE010 E3DL1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285506

CATALOG NUMBER: P3AS13R55B2750DE010 E3DL1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	245770
5°	243275
10°	234932
15°	217141
20°	187383
25°	148000
30°	104978
35°	67699
40°	40648
45°	22917
50°	12315
55°	4396
60°	3947
65°	3840
70°	3654
75°	3474
80°	3157
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22917 cd/sqm

TEST NUMBER: P1285506

CATALOG NUMBER: P3AS13R55B2750DE010 E3DL1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.9	11.6
10°-20°	264.5	29.6
20°-30°	277.2	31.0
30°-40°	161.7	18.1
40°-50°	60.5	6.8
50°-60°	14.2	1.6
60°-70°	7.3	0.8
70°-80°	4.3	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.6	72.1
0°-40°	807.4	90.2
0°-60°	882.1	98.6
0°-90°	895.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	895.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1121	
5°	1105	104
15°	956	265
25°	612	277
35°	253	162
45°	74	61
55°	12	14
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1285506

CATALOG NUMBER: P3AS13R55B2750DE010 E3DL1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1120.8
2.5°	1117.5
5°	1105.2
7.5°	1085.5
10°	1055.1
12.5°	1012.4
15°	956.5
17.5°	885.9
20°	803.0
22.5°	710.2
25°	611.7
27.5°	510.7
30°	414.6
32.5°	327.6
35°	252.9
37.5°	192.1
40°	142.0
42.5°	101.8
45°	73.9
47.5°	53.4
50°	36.1
52.5°	20.5
55°	11.5
57.5°	9.9
60°	9.0
62.5°	8.2
65°	7.4
67.5°	6.6
70°	5.7
72.5°	4.9
75°	4.1
77.5°	3.3
80°	2.5
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)