

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285537

Luminaire Tested: P3AS13R55B2750DE010 E3DLD1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLD1WH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 649.9 lumens
Efficiency: N/A
Efficacy: 34.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285537

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1WH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285537

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122227
5°	120647
10°	115896
15°	108400
20°	98895
25°	88239
30°	77176
35°	64112
40°	50552
45°	34267
50°	20946
55°	10857
60°	10087
65°	9547
70°	8848
75°	7795
80°	7703
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34267 cd/sqm

TEST NUMBER: P1285537

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.4	7.9
10°-20°	133.5	20.5
20°-30°	167.1	25.7
30°-40°	149.2	23.0
40°-50°	87.3	13.4
50°-60°	30.2	4.6
60°-70°	18.2	2.8
70°-80°	10.1	1.6
80°-90°	2.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.0	54.2
0°-40°	501.2	77.1
0°-60°	618.7	95.2
0°-90°	649.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	649.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	557	
5°	548	51
15°	478	133
25°	365	167
35°	240	149
45°	110	87
55°	28	30
65°	18	18
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1285537

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLD1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	557.4
2.5°	554.3
5°	548.1
7.5°	535.9
10°	520.5
12.5°	501.3
15°	477.5
17.5°	452.2
20°	423.8
22.5°	394.6
25°	364.7
27.5°	334.7
30°	304.8
32.5°	272.5
35°	239.5
37.5°	207.3
40°	176.6
42.5°	143.6
45°	110.5
47.5°	84.4
50°	61.4
52.5°	39.9
55°	28.4
57.5°	25.3
60°	23.0
62.5°	20.7
65°	18.4
67.5°	16.1
70°	13.8
72.5°	11.5
75°	9.2
77.5°	7.7
80°	6.1
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)