

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284590

Luminaire Tested: P3AS13R25B2750DE010 E3D1H_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25B2750DE010 E3D1H_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 80CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1040.1 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284590

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1H_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284590

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1H_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		100	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		98	97	96	94
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		96	94	93	92
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		90	88	86	85
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		88	86	84	83
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		86	84	82	81
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		84	82	80	79
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		83	80	78	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1138988
5°	1055115
10°	816351
15°	389923
20°	128555
25°	54197
30°	21016
35°	9075
40°	3034
45°	1395
50°	512
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1395 cd/sqm

TEST NUMBER: P1284590

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1H_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	421.3	40.5
10°-20°	479.2	46.1
20°-30°	111.4	10.7
30°-40°	23.4	2.2
40°-50°	3.8	0.4
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1011.9	97.3
0°-40°	1035.3	99.5
0°-60°	1039.7	100.0
0°-90°	1040.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1040.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5194	
5°	4793	421
15°	1718	479
25°	224	111
35°	34	23
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1284590

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1H_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5194.2
1°	5183.7
2°	5129.7
3°	5054.0
4°	4938.2
5°	4793.4
6°	4607.5
7°	4412.9
8°	4194.6
9°	3948.4
10°	3666.3
11°	3339.4
12°	2964.2
13°	2553.2
14°	2123.3
15°	1717.6
16°	1358.6
17°	1058.5
18°	832.6
19°	665.9
20°	550.9
21°	460.4
22°	386.5
23°	322.8
24°	270.0
25°	224.0
27.5°	132.7
30°	83.0
32.5°	53.2
35°	33.9
37.5°	20.4
40°	10.6
42.5°	6.8
45°	4.5
47.5°	2.6
50°	1.5
52.5°	0.8
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0



TEST NUMBER: P1284590

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1H_4000K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)