

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285549

Luminaire Tested: P3AS13R55B2750DE010 E3DLP1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285549
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLP1GPH_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 277.0 lumens
Efficiency: N/A
Efficacy: 14.5 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285549

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1285549

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94		92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87		85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	83	80		79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80	77	74		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69		67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	68	64		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68	63	60		59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56		55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53		52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58	53	50		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75345
5°	73453
10°	68291
15°	60818
20°	51688
25°	41712
30°	31802
35°	22620
40°	14914
45°	8838
50°	5185
55°	3211
60°	2851
65°	2542
70°	2180
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8838 cd/sqm

TEST NUMBER: P1285549

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.0	11.2
10°-20°	74.3	26.8
20°-30°	78.7	28.4
30°-40°	53.2	19.2
40°-50°	23.3	8.4
50°-60°	8.4	3.0
60°-70°	4.9	1.8
70°-80°	2.5	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.9	66.4
0°-40°	237.1	85.6
0°-60°	268.7	97.0
0°-90°	277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	344	
5°	334	31
15°	268	74
25°	172	79
35°	84	53
45°	28	23
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1285549

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	343.6
2.5°	341.0
5°	333.7
7.5°	321.9
10°	306.7
12.5°	288.5
15°	267.9
17.5°	245.1
20°	221.5
22.5°	196.7
25°	172.4
27.5°	148.4
30°	125.6
32.5°	103.9
35°	84.5
37.5°	67.0
40°	52.1
42.5°	39.2
45°	28.5
47.5°	20.9
50°	15.2
52.5°	10.7
55°	8.4
57.5°	7.6
60°	6.5
62.5°	5.7
65°	4.9
67.5°	4.2
70°	3.4
72.5°	3.0
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)