

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285551

Luminaire Tested: P3AS13R55B2750DE010 E3DLP1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLP1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 292.9 lumens
Efficiency: N/A
Efficacy: 15.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285551

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285551

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97	95	94	92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	83	80	79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80	77	74	73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76	72	69	67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68	63	60	59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64	60	56	55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61	56	53	52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58	53	50	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79709
5°	77702
10°	72232
15°	64336
20°	54675
25°	44107
30°	33625
35°	23932
40°	15772
45°	9365
50°	5492
55°	3403
60°	2982
65°	2698
70°	2308
75°	2033
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9365 cd/sqm

TEST NUMBER: P1285551

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.8	11.2
10°-20°	78.6	26.8
20°-30°	83.2	28.4
30°-40°	56.2	19.2
40°-50°	24.6	8.4
50°-60°	8.8	3.0
60°-70°	5.1	1.8
70°-80°	2.7	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.5	66.4
0°-40°	250.8	85.6
0°-60°	284.2	97.0
0°-90°	292.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	292.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	364	
5°	353	33
15°	283	79
25°	182	83
35°	89	56
45°	30	25
55°	9	9
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1285551

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	363.5
2.5°	360.7
5°	353.0
7.5°	340.5
10°	324.4
12.5°	305.1
15°	283.4
17.5°	259.2
20°	234.3
22.5°	208.1
25°	182.3
27.5°	157.0
30°	132.8
32.5°	109.9
35°	89.4
37.5°	70.8
40°	55.1
42.5°	41.5
45°	30.2
47.5°	22.1
50°	16.1
52.5°	11.3
55°	8.9
57.5°	8.1
60°	6.8
62.5°	6.0
65°	5.2
67.5°	4.4
70°	3.6
72.5°	3.2
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)