

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284611

Luminaire Tested: P3AS13R25B2750DE010 E3D1WMH_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25B2750DE010 E3D1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 80CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1110.0 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284611

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284611

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	96	96
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	93	93
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	91	91
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	88	88
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	86	86
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	84	84
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	82	82
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	80	80
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	78	78
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1215648
5°	1126125
10°	871304
15°	416166
20°	137212
25°	57850
30°	22409
35°	9690
40°	3235
45°	1489
50°	546
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1489 cd/sqm

TEST NUMBER: P1284611

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	449.7	40.5
10°-20°	511.5	46.1
20°-30°	118.9	10.7
30°-40°	24.9	2.2
40°-50°	4.0	0.4
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1080.0	97.3
0°-40°	1104.9	99.5
0°-60°	1109.6	100.0
0°-90°	1110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5544	
5°	5116	450
15°	1833	511
25°	239	119
35°	36	25
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1284611

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5543.8
1°	5532.6
2°	5475.0
3°	5394.1
4°	5270.6
5°	5116.0
6°	4917.6
7°	4710.0
8°	4476.9
9°	4214.1
10°	3913.1
11°	3564.2
12°	3163.7
13°	2725.0
14°	2266.2
15°	1833.2
16°	1450.1
17°	1129.7
18°	888.6
19°	710.7
20°	588.0
21°	491.4
22°	412.5
23°	344.5
24°	288.2
25°	239.1
27.5°	141.7
30°	88.5
32.5°	56.7
35°	36.2
37.5°	21.7
40°	11.3
42.5°	7.2
45°	4.8
47.5°	2.8
50°	1.6
52.5°	0.8
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0

TEST NUMBER: P1284611

CATALOG NUMBER: P3AS13R25B2750DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)