

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285572

Luminaire Tested: P3AS13R55B2750DE010 E3DLP1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285572
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55B2750DE010 E3DLP1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 558.0 lumens
Efficiency: N/A
Efficacy: 29.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285572

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WMH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1285572

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151786
5°	147986
10°	137584
15°	122521
20°	104122
25°	84029
30°	64060
35°	45561
40°	30056
45°	17831
50°	10473
55°	6461
60°	5701
65°	5189
70°	4424
75°	3897
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17831 cd/sqm

TEST NUMBER: P1285572

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	11.2
10°-20°	149.6	26.8
20°-30°	158.5	28.4
30°-40°	107.1	19.2
40°-50°	47.0	8.4
50°-60°	16.8	3.0
60°-70°	9.9	1.8
70°-80°	5.1	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.5	66.4
0°-40°	477.6	85.6
0°-60°	541.4	97.0
0°-90°	558.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	558.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	692	
5°	672	62
15°	540	150
25°	347	158
35°	170	107
45°	58	47
55°	17	17
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1285572

CATALOG NUMBER: P3AS13R55B2750DE010 E3DLP1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	692.2
2.5°	686.9
5°	672.3
7.5°	648.5
10°	617.9
12.5°	581.1
15°	539.7
17.5°	493.7
20°	446.2
22.5°	396.3
25°	347.3
27.5°	299.0
30°	253.0
32.5°	209.3
35°	170.2
37.5°	134.9
40°	105.0
42.5°	79.0
45°	57.5
47.5°	42.2
50°	30.7
52.5°	21.5
55°	16.9
57.5°	15.3
60°	13.0
62.5°	11.5
65°	10.0
67.5°	8.4
70°	6.9
72.5°	6.1
75°	4.6
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)