

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285583

Luminaire Tested: P3AS13R60B2750DE010 E3CB1MMS\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285583  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R60B2750DE010 E3CB1MMS\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 978.1 lumens  
Efficiency: N/A  
Efficacy: 51.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285583

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MMS\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1285583

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MMS\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 100 | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 96  | 106 | 102 | 98  | 95  | 98  | 95  | 93  |  | 95  | 93  | 91  |  | 93  |
| 3   | 103 | 96  | 91  | 88  | 101 | 95  | 90  | 87  | 92  | 89  | 85  |  | 90  | 87  | 84  |  | 88  |
| 4   | 98  | 90  | 85  | 81  | 96  | 89  | 84  | 80  | 87  | 83  | 79  |  | 85  | 81  | 78  |  | 83  |
| 5   | 93  | 84  | 79  | 74  | 91  | 84  | 78  | 74  | 82  | 77  | 73  |  | 80  | 76  | 73  |  | 79  |
| 6   | 88  | 79  | 73  | 69  | 87  | 78  | 73  | 69  | 77  | 72  | 68  |  | 76  | 71  | 68  |  | 74  |
| 7   | 84  | 75  | 69  | 64  | 82  | 74  | 68  | 64  | 73  | 68  | 64  |  | 71  | 67  | 64  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 56  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 233534 |
| 5°  | 224279 |
| 10° | 230902 |
| 15° | 233872 |
| 20° | 206518 |
| 25° | 174058 |
| 30° | 141161 |
| 35° | 91926  |
| 40° | 42222  |
| 45° | 16188  |
| 50° | 5424   |
| 55° | 1453   |
| 60° | 1316   |
| 65° | 1193   |
| 70° | 962    |
| 75° | 1271   |
| 80° | 1010   |
| 85° | 2013   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16188 cd/sqm

TEST NUMBER: P1285583

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MMS\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 98.1   | 10.0      |
| 10°-20°   | 282.1  | 28.8      |
| 20°-30°   | 329.1  | 33.6      |
| 30°-40°   | 212.3  | 21.7      |
| 40°-50°   | 47.6   | 4.9       |
| 50°-60°   | 4.8    | 0.5       |
| 60°-70°   | 2.3    | 0.2       |
| 70°-80°   | 1.3    | 0.1       |
| 80°-90°   | 0.5    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 709.3  | 72.5      |
| 0°-40°    | 921.6  | 94.2      |
| 0°-60°    | 973.9  | 99.6      |
| 0°-90°    | 978.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 978.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1065 |      |
| 5°  | 1019 | 98   |
| 15° | 1030 | 282  |
| 25° | 719  | 329  |
| 35° | 343  | 212  |
| 45° | 52   | 48   |
| 55° | 4    | 5    |
| 65° | 2    | 2    |
| 75° | 2    | 1    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1285583

CATALOG NUMBER: P3AS13R60B2750DE010 E3CB1MMS\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1065.0 |
| 2.5°  | 1047.6 |
| 5°    | 1018.9 |
| 7.5°  | 1017.4 |
| 10°   | 1037.0 |
| 12.5° | 1049.9 |
| 15°   | 1030.2 |
| 17.5° | 971.2  |
| 20°   | 885.0  |
| 22.5° | 795.0  |
| 25°   | 719.4  |
| 27.5° | 645.2  |
| 30°   | 557.5  |
| 32.5° | 454.6  |
| 35°   | 343.4  |
| 37.5° | 234.5  |
| 40°   | 147.5  |
| 42.5° | 88.5   |
| 45°   | 52.2   |
| 47.5° | 30.3   |
| 50°   | 15.9   |
| 52.5° | 5.3    |
| 55°   | 3.8    |
| 57.5° | 3.0    |
| 60°   | 3.0    |
| 62.5° | 2.3    |
| 65°   | 2.3    |
| 67.5° | 2.3    |
| 70°   | 1.5    |
| 72.5° | 1.5    |
| 75°   | 1.5    |
| 77.5° | 0.8    |
| 80°   | 0.8    |
| 82.5° | 0.8    |
| 85°   | 0.8    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)