

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284687

Luminaire Tested: P3AS13R25B2750DE010 E3DLP1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284687
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25B2750DE010 E3DLP1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 492.0 lumens
Efficiency: N/A
Efficacy: 25.8 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284687

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1284687

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82	79	76	75
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78	74	71	70
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74	70	67	66
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70	66	63	62
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64	59	56	55
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61	57	54	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	178626
5°	171362
10°	150120
15°	120682
20°	92711
25°	70141
30°	50691
35°	33676
40°	20410
45°	11908
50°	7573
55°	6155
60°	5394
65°	4774
70°	3911
75°	3897
80°	2904
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11908 cd/sqm

TEST NUMBER: P1284687

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.9	14.4
10°-20°	147.0	29.9
20°-30°	132.9	27.0
30°-40°	79.9	16.2
40°-50°	31.7	6.4
50°-60°	14.6	3.0
60°-70°	8.9	1.8
70°-80°	4.7	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	350.8	71.3
0°-40°	430.6	87.5
0°-60°	477.0	96.9
0°-90°	492.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	815	
5°	778	71
15°	532	147
25°	290	133
35°	126	80
45°	38	32
55°	16	15
65°	9	9
75°	5	5
85°	2	1
90°	0	

TEST NUMBER: P1284687

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	814.6
1°	814.6
2°	810.8
3°	802.3
4°	791.6
5°	778.5
6°	761.7
7°	742.5
8°	720.2
9°	698.0
10°	674.2
11°	646.6
12°	618.2
13°	589.8
14°	561.5
15°	531.6
17.5°	461.0
20°	397.3
22.5°	339.8
25°	289.9
27.5°	243.1
30°	200.2
32.5°	161.1
35°	125.8
37.5°	95.9
40°	71.3
42.5°	52.2
45°	38.4
47.5°	29.1
50°	22.2
52.5°	18.4
55°	16.1
57.5°	13.8
60°	12.3
62.5°	10.0
65°	9.2
67.5°	7.7
70°	6.1
72.5°	5.4
75°	4.6
77.5°	3.8
80°	2.3
82.5°	1.5
85°	1.5
87.5°	0.8



TEST NUMBER: P1284687

CATALOG NUMBER: P3AS13R25B2750DE010 E3DLP1MW_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)