

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284776

Luminaire Tested: P3AS13R30B2750DE010 E3DL1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30B2750DE010 E3DL1GPH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 80CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 426.0 lumens
Efficiency: N/A
Efficacy: 22.3 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284776

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284776

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90			
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86			
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82			
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78			
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75			
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71			
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69			
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66			
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248577
5°	236605
10°	199017
15°	143520
20°	89024
25°	50640
30°	28131
35°	15285
40°	8072
45°	4373
50°	2320
55°	1529
60°	1403
65°	1453
70°	1282
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4373 cd/sqm

TEST NUMBER: P1284776

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.8	22.7
10°-20°	172.0	40.4
20°-30°	99.4	23.3
30°-40°	37.7	8.9
40°-50°	11.6	2.7
50°-60°	3.9	0.9
60°-70°	2.6	0.6
70°-80°	1.4	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.3	86.5
0°-40°	406.0	95.3
0°-60°	421.5	98.9
0°-90°	426.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	426.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1134	
5°	1075	97
15°	632	172
25°	209	99
35°	57	38
45°	14	12
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1284776

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1133.6
1°	1132.8
2°	1126.0
3°	1113.1
4°	1097.0
5°	1074.9
6°	1046.7
7°	1015.3
8°	980.3
9°	938.5
10°	893.8
11°	845.5
12°	794.4
13°	740.9
14°	686.5
15°	632.2
17.5°	498.6
20°	381.5
22.5°	282.9
25°	209.3
27.5°	152.1
30°	111.1
32.5°	80.1
35°	57.1
37.5°	39.8
40°	28.2
42.5°	19.7
45°	14.1
47.5°	9.7
50°	6.8
52.5°	4.8
55°	4.0
57.5°	3.6
60°	3.2
62.5°	2.8
65°	2.8
67.5°	2.4
70°	2.0
72.5°	1.6
75°	1.2
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0



TEST NUMBER: P1284776

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)