

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284782

Luminaire Tested: P3AS13R30B2750DE010 E3DL1LI\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1284782  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30B2750DE010 E3DL1LI\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 813.0 lumens  
Efficiency: N/A  
Efficacy: 42.6 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1284782  
CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1284782  
 CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	92	92	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	87	87	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	83	83	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	79	79	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	76	76	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	73	73	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	70	70	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	67	67	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	65	65	65	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	474414
5°	451551
10°	379819
15°	273895
20°	169905
25°	96635
30°	53679
35°	29205
40°	15400
45°	8342
50°	4469
55°	2944
60°	2675
65°	2802
70°	2436
75°	1949
80°	1894
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8342 cd/sqm



TEST NUMBER: P1284782

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	184.7	22.7
10°-20°	328.4	40.4
20°-30°	189.8	23.3
30°-40°	72.0	8.9
40°-50°	22.1	2.7
50°-60°	7.4	0.9
60°-70°	5.0	0.6
70°-80°	2.7	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	702.8	86.4
0°-40°	774.9	95.3
0°-60°	804.4	98.9
0°-90°	813.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	813.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2164	
5°	2051	185
15°	1206	328
25°	399	190
35°	109	72
45°	27	22
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1284782  
CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2163.5
1°	2162.0
2°	2148.9
3°	2124.3
4°	2093.6
5°	2051.4
6°	1997.6
7°	1937.7
8°	1870.9
9°	1791.0
10°	1705.8
11°	1613.6
12°	1516.1
13°	1413.9
14°	1310.2
15°	1206.5
17.5°	951.6
20°	728.1
22.5°	539.9
25°	399.4
27.5°	290.3
30°	212.0
32.5°	152.8
35°	109.1
37.5°	76.0
40°	53.8
42.5°	37.6
45°	26.9
47.5°	18.4
50°	13.1
52.5°	9.2
55°	7.7
57.5°	6.9
60°	6.1
62.5°	5.4
65°	5.4
67.5°	4.6
70°	3.8
72.5°	3.1
75°	2.3
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.0



TEST NUMBER: P1284782  
CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI\_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)