

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284783

Luminaire Tested: P3AS13R30B2750DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30B2750DE010 E3DL1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 801.0 lumens
Efficiency: N/A
Efficacy: 41.9 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284783
CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284783

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	92	92	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	87	87	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	83	83	83	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	79	79	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	76	76	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	73	73	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	70	70	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	67	67	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	65	65	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	467419
5°	444881
10°	374208
15°	269854
20°	167385
25°	95207
30°	52869
35°	28750
40°	15171
45°	8218
50°	4401
55°	2906
60°	2675
65°	2750
70°	2436
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8218 cd/sqm



TEST NUMBER: P1284783

CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	22.7
10°-20°	323.5	40.4
20°-30°	187.0	23.3
30°-40°	71.0	8.9
40°-50°	21.8	2.7
50°-60°	7.4	0.9
60°-70°	5.0	0.6
70°-80°	2.7	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	692.4	86.4
0°-40°	763.4	95.3
0°-60°	792.5	98.9
0°-90°	801.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	801.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2132	
5°	2021	182
15°	1189	323
25°	394	187
35°	107	71
45°	26	22
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1284783
CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2131.6
1°	2130.0
2°	2117.2
3°	2093.0
4°	2062.7
5°	2021.1
6°	1968.1
7°	1909.1
8°	1843.3
9°	1764.6
10°	1680.6
11°	1589.8
12°	1493.7
13°	1393.0
14°	1290.9
15°	1188.7
17.5°	937.5
20°	717.3
22.5°	531.9
25°	393.5
27.5°	286.0
30°	208.8
32.5°	150.6
35°	107.4
37.5°	74.9
40°	53.0
42.5°	37.1
45°	26.5
47.5°	18.2
50°	12.9
52.5°	9.1
55°	7.6
57.5°	6.8
60°	6.1
62.5°	5.3
65°	5.3
67.5°	4.5
70°	3.8
72.5°	3.0
75°	2.3
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.0



TEST NUMBER: P1284783
CATALOG NUMBER: P3AS13R30B2750DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)