

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285691

Luminaire Tested: P3AS13R60B2750DE010 E3DLD1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60B2750DE010 E3DLD1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 677.0 lumens
Efficiency: N/A
Efficacy: 35.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285691

CATALOG NUMBER: P3AS13R60B2750DE010 E3DLD1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285691

CATALOG NUMBER: P3AS13R60B2750DE010 E3DLD1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44		
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120188
5°	118820
10°	114716
15°	108377
20°	99899
25°	90465
30°	80316
35°	68636
40°	54559
45°	38485
50°	22993
55°	11622
60°	11183
65°	10222
70°	9489
75°	9065
80°	8334
85°	6290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38485 cd/sqm

TEST NUMBER: P1285691

CATALOG NUMBER: P3AS13R60B2750DE010 E3DLD1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	7.5
10°-20°	133.4	19.7
20°-30°	171.3	25.3
30°-40°	158.8	23.5
40°-50°	96.7	14.3
50°-60°	32.2	4.8
60°-70°	19.6	2.9
70°-80°	11.0	1.6
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.5	52.5
0°-40°	514.3	76.0
0°-60°	643.2	95.0
0°-90°	677.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	548	
5°	540	51
15°	477	133
25°	374	171
35°	256	159
45°	124	97
55°	30	32
65°	20	20
75°	11	11
85°	2	3
90°	0	

TEST NUMBER: P1285691

CATALOG NUMBER: P3AS13R60B2750DE010 E3DLD1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	548.1
2.5°	545.6
5°	539.8
7.5°	529.2
10°	515.2
12.5°	497.9
15°	477.4
17.5°	453.6
20°	428.1
22.5°	401.0
25°	373.9
27.5°	345.9
30°	317.2
32.5°	288.4
35°	256.4
37.5°	222.7
40°	190.6
42.5°	156.9
45°	124.1
47.5°	96.1
50°	67.4
52.5°	40.3
55°	30.4
57.5°	27.9
60°	25.5
62.5°	22.2
65°	19.7
67.5°	17.3
70°	14.8
72.5°	12.3
75°	10.7
77.5°	8.2
80°	6.6
82.5°	4.1
85°	2.5
87.5°	1.6
90°	0.0

(END OF REPORT)