

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284802

Luminaire Tested: P3AS13R30B2750DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30B2750DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 306.0 lumens
Efficiency: N/A
Efficacy: 16.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284802

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1284802

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	72297
5°	70658
10°	65708
15°	58479
20°	50288
25°	42607
30°	35373
35°	27733
40°	19894
45°	13056
50°	7437
55°	4893
60°	4605
65°	4307
70°	3847
75°	3474
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13056 cd/sqm

TEST NUMBER: P1284802

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.8	9.7
10°-20°	71.6	23.4
20°-30°	80.7	26.4
30°-40°	64.5	21.1
40°-50°	33.1	10.8
50°-60°	12.5	4.1
60°-70°	8.2	2.7
70°-80°	4.4	1.4
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	182.1	59.5
0°-40°	246.6	80.6
0°-60°	292.2	95.5
0°-90°	306.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	306.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	330	
5°	321	30
15°	258	72
25°	176	81
35°	104	64
45°	42	33
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1284802

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	329.7
1°	329.7
2°	328.6
3°	326.7
4°	324.0
5°	321.0
6°	317.3
7°	312.4
8°	307.2
9°	301.1
10°	295.1
11°	288.4
12°	281.2
13°	273.7
14°	265.8
15°	257.6
17.5°	236.6
20°	215.5
22.5°	195.3
25°	176.1
27.5°	157.3
30°	139.7
32.5°	121.7
35°	103.6
37.5°	86.0
40°	69.5
42.5°	54.8
45°	42.1
47.5°	31.2
50°	21.8
52.5°	15.4
55°	12.8
57.5°	11.6
60°	10.5
62.5°	9.4
65°	8.3
67.5°	7.1
70°	6.0
72.5°	4.9
75°	4.1
77.5°	3.4
80°	2.6
82.5°	1.9
85°	1.1
87.5°	0.4



TEST NUMBER: P1284802

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)