

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285761

Luminaire Tested: P3AS13R65B2750DE010 E3D1LI\_5000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1285761  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R65B2750DE010 E3D1LI\_5000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 80CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 980.0 lumens  
Efficiency: N/A  
Efficacy: 51.3 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1285761

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1LI\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1285761

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1LI\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 102 |  | 101 | 100 | 99  |  | 98  |
| 2   | 108 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 99  | 96  | 93  |  | 96  | 93  | 91  |  | 93  |
| 3   | 103 | 97  | 92  | 88  | 101 | 95  | 91  | 88  | 93  | 89  | 86  |  | 90  | 87  | 85  |  | 88  |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  | 87  | 83  | 80  |  | 85  | 82  | 79  |  | 84  |
| 5   | 93  | 85  | 79  | 75  | 92  | 84  | 79  | 75  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  |  | 76  | 72  | 69  |  | 75  |
| 7   | 84  | 75  | 70  | 65  | 83  | 75  | 69  | 65  | 73  | 69  | 65  |  | 72  | 68  | 65  |  | 71  |
| 8   | 80  | 71  | 65  | 61  | 79  | 71  | 65  | 61  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  |
| 9   | 77  | 67  | 61  | 58  | 76  | 67  | 61  | 57  | 66  | 61  | 57  |  | 65  | 60  | 57  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  |  | 62  | 57  | 54  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 262589 |
| 5°  | 243825 |
| 10° | 235801 |
| 15° | 227243 |
| 20° | 210088 |
| 25° | 191406 |
| 30° | 147896 |
| 35° | 85715  |
| 40° | 34007  |
| 45° | 14482  |
| 50° | 3446   |
| 55° | 459    |
| 60° | 351    |
| 65° | 208    |
| 70° | 256    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14482 cd/sqm

TEST NUMBER: P1285761

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1LI\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 104.5  | 10.7      |
| 10°-20°   | 278.9  | 28.5      |
| 20°-30°   | 353.0  | 36.0      |
| 30°-40°   | 201.0  | 20.5      |
| 40°-50°   | 39.9   | 4.1       |
| 50°-60°   | 2.1    | 0.2       |
| 60°-70°   | 0.5    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 736.4  | 75.1      |
| 0°-40°    | 937.4  | 95.7      |
| 0°-60°    | 979.4  | 99.9      |
| 0°-90°    | 980.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 980.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1198 |      |
| 5°  | 1108 | 104  |
| 15° | 1001 | 279  |
| 25° | 791  | 353  |
| 35° | 320  | 201  |
| 45° | 47   | 40   |
| 55° | 1    | 2    |
| 65° | 0    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1285761

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1197.5 |
| 1°    | 1188.7 |
| 2°    | 1169.3 |
| 3°    | 1146.8 |
| 4°    | 1124.6 |
| 5°    | 1107.7 |
| 6°    | 1095.2 |
| 7°    | 1085.2 |
| 8°    | 1076.3 |
| 9°    | 1067.4 |
| 10°   | 1059.0 |
| 11°   | 1049.7 |
| 12°   | 1040.0 |
| 13°   | 1028.4 |
| 14°   | 1015.9 |
| 15°   | 1001.0 |
| 16°   | 983.2  |
| 17°   | 963.9  |
| 18°   | 943.0  |
| 19°   | 920.8  |
| 20°   | 900.3  |
| 21°   | 879.3  |
| 22°   | 860.4  |
| 23°   | 840.7  |
| 24°   | 817.7  |
| 25°   | 791.1  |
| 26°   | 759.3  |
| 27°   | 721.0  |
| 28°   | 677.9  |
| 29°   | 632.0  |
| 30°   | 584.1  |
| 31°   | 531.3  |
| 32°   | 478.9  |
| 32.5° | 451.9  |
| 33°   | 425.8  |
| 34°   | 372.6  |
| 35°   | 320.2  |
| 36°   | 271.9  |
| 37°   | 224.0  |
| 37.5° | 199.4  |
| 38°   | 179.7  |
| 39°   | 145.4  |
| 40°   | 118.8  |
| 42.5° | 73.3   |
| 45°   | 46.7   |



TEST NUMBER: P1285761

CATALOG NUMBER: P3AS13R65B2750DE010 E3D1LI\_5000K

**CANDELA DISTRIBUTION (continued):**

|       | 0°   |
|-------|------|
| 47.5° | 27.4 |
| 50°   | 10.1 |
| 52.5° | 2.0  |
| 55°   | 1.2  |
| 57.5° | 0.8  |
| 60°   | 0.8  |
| 62.5° | 0.8  |
| 65°   | 0.4  |
| 67.5° | 0.4  |
| 70°   | 0.4  |
| 72.5° | 0.0  |
| 75°   | 0.0  |
| 77.5° | 0.0  |
| 80°   | 0.0  |
| 82.5° | 0.0  |
| 85°   | 0.0  |
| 87.5° | 0.0  |
| 90°   | 0.0  |

(END OF REPORT)