

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285796

Luminaire Tested: P3AS13R65B2750DE010 E3DL1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65B2750DE010 E3DL1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 824.0 lumens
Efficiency: N/A
Efficacy: 43.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285796

CATALOG NUMBER: P3AS13R65B2750DE010 E3DL1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285796

CATALOG NUMBER: P3AS13R65B2750DE010 E3DL1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63		
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194327
5°	191987
10°	184699
15°	173032
20°	155624
25°	132153
30°	103358
35°	73642
40°	48205
45°	29802
50°	15147
55°	5352
60°	4693
65°	4670
70°	4231
75°	4151
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 29802 cd/sqm

TEST NUMBER: P1285796

CATALOG NUMBER: P3AS13R65B2750DE010 E3DL1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.9	9.9
10°-20°	212.1	25.7
20°-30°	247.9	30.1
30°-40°	173.2	21.0
40°-50°	76.3	9.3
50°-60°	17.0	2.1
60°-70°	8.6	1.0
70°-80°	5.2	0.6
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	541.9	65.8
0°-40°	715.2	86.8
0°-60°	808.4	98.1
0°-90°	824.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	824.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	886	
5°	872	82
15°	762	212
25°	546	248
35°	275	173
45°	96	76
55°	14	17
65°	9	9
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1285796

CATALOG NUMBER: P3AS13R65B2750DE010 E3DL1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	886.2
2.5°	882.9
5°	872.2
7.5°	854.2
10°	829.5
12.5°	799.1
15°	762.2
17.5°	717.0
20°	666.9
22.5°	610.2
25°	546.2
27.5°	478.8
30°	408.2
32.5°	340.0
35°	275.1
37.5°	218.5
40°	168.4
42.5°	127.3
45°	96.1
47.5°	70.6
50°	44.4
52.5°	23.0
55°	14.0
57.5°	12.3
60°	10.7
62.5°	9.9
65°	9.0
67.5°	7.4
70°	6.6
72.5°	5.7
75°	4.9
77.5°	4.1
80°	3.3
82.5°	2.5
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)