

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284860

Luminaire Tested: P3AS13R30B2750DE010 E3DLP1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284860
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30B2750DE010 E3DLP1WMH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 80CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 496.0 lumens
Efficiency: N/A
Efficacy: 26.0 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284860

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLP1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284860

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLP1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169482
5°	164208
10°	147960
15°	122384
20°	94765
25°	71085
30°	51603
35°	34372
40°	21125
45°	12404
50°	7607
55°	6193
60°	5394
65°	4410
70°	3975
75°	3897
80°	2904
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12404 cd/sqm

TEST NUMBER: P1284860

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLP1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	13.8
10°-20°	148.5	29.9
20°-30°	135.1	27.2
30°-40°	81.7	16.5
40°-50°	32.7	6.6
50°-60°	14.5	2.9
60°-70°	8.8	1.8
70°-80°	4.8	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.2	71.0
0°-40°	433.9	87.5
0°-60°	481.1	97.0
0°-90°	496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	773	
5°	746	69
15°	539	148
25°	294	135
35°	128	82
45°	40	33
55°	16	15
65°	8	9
75°	5	5
85°	2	1
90°	0	

TEST NUMBER: P1284860

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLP1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	772.9
1°	772.2
2°	769.1
3°	763.7
4°	756.0
5°	746.0
6°	733.7
7°	720.6
8°	703.7
9°	684.5
10°	664.5
11°	641.4
12°	616.8
13°	592.2
14°	565.3
15°	539.1
17.5°	470.7
20°	406.1
22.5°	346.1
25°	293.8
27.5°	246.1
30°	203.8
32.5°	164.6
35°	128.4
37.5°	98.4
40°	73.8
42.5°	53.8
45°	40.0
47.5°	30.0
50°	22.3
52.5°	17.7
55°	16.2
57.5°	13.8
60°	12.3
62.5°	10.0
65°	8.5
67.5°	7.7
70°	6.2
72.5°	5.4
75°	4.6
77.5°	3.8
80°	2.3
82.5°	1.5
85°	1.5
87.5°	0.8



TEST NUMBER: P1284860

CATALOG NUMBER: P3AS13R30B2750DE010 E3DLP1WMH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)