

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284890

Luminaire Tested: P3AS13R35B2750DE010 E3CB1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35B2750DE010 E3CB1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 80CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 977.0 lumens
Efficiency: N/A
Efficacy: 51.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284890

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284890

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	637076
5°	624079
10°	580595
15°	425655
20°	217976
25°	78561
30°	30587
35°	10708
40°	4408
45°	1178
50°	1058
55°	1185
60°	1009
65°	778
70°	962
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 1344 cd/sqm

TEST NUMBER: P1284890

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.3	27.1
10°-20°	495.9	50.8
20°-30°	175.6	18.0
30°-40°	30.7	3.1
40°-50°	4.5	0.5
50°-60°	2.5	0.3
60°-70°	1.8	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.8	95.8
0°-40°	966.6	98.9
0°-60°	973.6	99.7
0°-90°	977.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	977.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2905	
5°	2835	264
15°	1875	496
25°	325	176
35°	40	31
45°	4	4
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1284890

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2905.3
1°	2904.5
2°	2895.3
3°	2877.6
4°	2861.4
5°	2835.2
6°	2808.3
7°	2778.3
8°	2741.4
9°	2683.7
10°	2607.5
11°	2502.1
12°	2375.1
13°	2224.3
14°	2058.2
15°	1875.0
17.5°	1396.5
20°	934.1
22.5°	563.2
25°	324.7
27.5°	193.9
30°	120.8
32.5°	70.0
35°	40.0
37.5°	25.4
40°	15.4
42.5°	7.7
45°	3.8
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P1284890

CATALOG NUMBER: P3AS13R35B2750DE010 E3CB1MW_4000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)