

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284922

Luminaire Tested: P3AS13R35B2750DE010 E3DL1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35B2750DE010 E3DL1LI_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 806.0 lumens
Efficiency: N/A
Efficacy: 42.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284922
CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1284922
 CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1LI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	406503
5°	390688
10°	340408
15°	260728
20°	174432
25°	105538
30°	60566
35°	33863
40°	18005
45°	9272
50°	4435
55°	3517
60°	3377
65°	2802
70°	2949
75°	2626
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9272 cd/sqm



TEST NUMBER: P1284922
 CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.5	20.0
10°-20°	312.9	38.8
20°-30°	204.9	25.4
30°-40°	83.1	10.3
40°-50°	24.9	3.1
50°-60°	8.5	1.1
60°-70°	5.7	0.7
70°-80°	3.3	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	679.3	84.3
0°-40°	762.4	94.6
0°-60°	795.8	98.7
0°-90°	806.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	806.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1854	
5°	1775	161
15°	1148	313
25°	436	205
35°	126	83
45°	30	25
55°	9	8
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1284922
CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1853.8
1°	1850.8
2°	1842.3
3°	1825.5
4°	1805.5
5°	1774.9
6°	1736.5
7°	1693.6
8°	1645.3
9°	1590.1
10°	1528.8
11°	1460.5
12°	1389.2
13°	1309.5
14°	1233.6
15°	1148.5
17.5°	942.3
20°	747.5
22.5°	575.0
25°	436.2
27.5°	325.1
30°	239.2
32.5°	175.6
35°	126.5
37.5°	89.7
40°	62.9
42.5°	43.7
45°	29.9
47.5°	19.9
50°	13.0
52.5°	10.0
55°	9.2
57.5°	8.4
60°	7.7
62.5°	6.9
65°	5.4
67.5°	4.6
70°	4.6
72.5°	3.8
75°	3.1
77.5°	2.3
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1284922
CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1LI_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)