

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284930

Luminaire Tested: P3AS13R35B2750DE010 E3DL1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35B2750DE010 E3DL1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 80CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 808.0 lumens
Efficiency: N/A
Efficacy: 42.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284930

CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1284930

CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407511
5°	391656
10°	341254
15°	261364
20°	174875
25°	105804
30°	60718
35°	33943
40°	18034
45°	9303
50°	4469
55°	3517
60°	3377
65°	2802
70°	2949
75°	2626
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9303 cd/sqm

TEST NUMBER: P1284930

CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.9	20.0
10°-20°	313.7	38.8
20°-30°	205.4	25.4
30°-40°	83.3	10.3
40°-50°	25.0	3.1
50°-60°	8.5	1.1
60°-70°	5.7	0.7
70°-80°	3.3	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.0	84.3
0°-40°	764.3	94.6
0°-60°	797.8	98.7
0°-90°	808.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	808.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1858	
5°	1779	162
15°	1151	314
25°	437	205
35°	127	83
45°	30	25
55°	9	9
65°	5	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1284930

CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1858.4
1°	1855.4
2°	1846.9
3°	1830.0
4°	1810.0
5°	1779.3
6°	1740.8
7°	1697.8
8°	1649.4
9°	1594.0
10°	1532.6
11°	1464.2
12°	1392.7
13°	1312.7
14°	1236.7
15°	1151.3
17.5°	944.6
20°	749.4
22.5°	576.4
25°	437.3
27.5°	325.9
30°	239.8
32.5°	176.0
35°	126.8
37.5°	89.9
40°	63.0
42.5°	43.8
45°	30.0
47.5°	20.0
50°	13.1
52.5°	10.0
55°	9.2
57.5°	8.5
60°	7.7
62.5°	6.9
65°	5.4
67.5°	4.6
70°	4.6
72.5°	3.8
75°	3.1
77.5°	2.3
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1284930

CATALOG NUMBER: P3AS13R35B2750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)