

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1284965

Luminaire Tested: P3AS13R35B2750DE010 E3DLD1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1284965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35B2750DE010 E3DLD1WH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 4000K CCT AND, 80CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 622.0 lumens
Efficiency: N/A
Efficacy: 32.6 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1284965

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1284965

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1WH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	112	109	106	104		110	107	104	102		103	101	99		99	98	96		96	94	93		91			
2	106	100	96	92		104	98	94	91		95	92	89		92	89	87		89	87	85		83			
3	100	92	87	82		98	91	86	81		88	84	80		86	82	79		83	80	78		76			
4	94	85	79	74		92	84	78	74		82	77	73		80	75	72		78	74	71		69			
5	89	79	73	68		87	78	72	67		76	71	67		75	70	66		73	69	66		64			
6	84	74	67	62		82	73	67	62		71	66	61		70	65	61		68	64	61		59			
7	79	69	62	57		78	68	62	57		67	61	57		65	60	57		64	60	56		55			
8	75	64	58	53		74	64	57	53		63	57	53		62	56	53		61	56	52		51			
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49		48			
10	67	57	51	46		66	56	50	46		56	50	46		55	50	46		54	49	46		45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142094
5°	139071
10°	130236
15°	116913
20°	101696
25°	86666
30°	72593
35°	57822
40°	41793
45°	26452
50°	14430
55°	9978
60°	9429
65°	8769
70°	8399
75°	7202
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26452 cd/sqm

TEST NUMBER: P1284965

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.8	9.5
10°-20°	143.3	23.0
20°-30°	164.2	26.4
30°-40°	134.0	21.5
40°-50°	67.6	10.9
50°-60°	25.1	4.0
60°-70°	16.8	2.7
70°-80°	9.3	1.5
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.4	58.9
0°-40°	500.4	80.4
0°-60°	593.0	95.3
0°-90°	622.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	622.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	632	59
15°	515	143
25°	358	164
35°	216	134
45°	85	68
55°	26	25
65°	17	17
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1284965

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	648.0
1°	647.2
2°	645.6
3°	642.6
4°	638.0
5°	631.8
6°	624.1
7°	616.4
8°	606.4
9°	596.5
10°	584.9
11°	572.6
12°	559.6
13°	545.0
14°	529.6
15°	515.0
17.5°	475.8
20°	435.8
22.5°	395.1
25°	358.2
27.5°	322.1
30°	286.7
32.5°	251.3
35°	216.0
37.5°	180.6
40°	146.0
42.5°	113.8
45°	85.3
47.5°	61.5
50°	42.3
52.5°	30.7
55°	26.1
57.5°	23.8
60°	21.5
62.5°	19.2
65°	16.9
67.5°	14.6
70°	13.1
72.5°	10.8
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	1.5



TEST NUMBER: P1284965

CATALOG NUMBER: P3AS13R35B2750DE010 E3DLD1WH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)