

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285133

Luminaire Tested: P3AS13R40B2750DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285133
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40B2750DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 272.0 lumens
Efficiency: N/A
Efficacy: 14.2 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285133

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1285133

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLP1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92	89	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86	84	81	80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	79	76	74
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77	74	71	69
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73	69	66	65
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70	66	62	61
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66	62	59	58
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63	59	56	54
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84686
5°	82985
10°	77264
15°	67333
20°	54278
25°	40672
30°	28587
35°	18738
40°	11336
45°	6760
50°	4060
55°	3250
60°	2938
65°	2491
70°	2372
75°	1864
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6760 cd/sqm

TEST NUMBER: P1285133

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.0	12.9
10°-20°	81.7	30.0
20°-30°	77.0	28.3
30°-40°	44.5	16.4
40°-50°	17.7	6.5
50°-60°	7.9	2.9
60°-70°	4.9	1.8
70°-80°	2.6	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	193.7	71.2
0°-40°	238.2	87.6
0°-60°	263.8	97.0
0°-90°	272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	386	
5°	377	35
15°	297	82
25°	168	77
35°	70	45
45°	22	18
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1285133

CATALOG NUMBER: P3AS13R40B2750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	386.2
2.5°	384.0
5°	377.0
7.5°	364.0
10°	347.0
12.5°	324.0
15°	296.6
17.5°	265.9
20°	232.6
22.5°	199.2
25°	168.1
27.5°	139.2
30°	112.9
32.5°	90.0
35°	70.0
37.5°	53.0
40°	39.6
42.5°	29.6
45°	21.8
47.5°	15.9
50°	11.9
52.5°	9.6
55°	8.5
57.5°	7.8
60°	6.7
62.5°	5.6
65°	4.8
67.5°	4.1
70°	3.7
72.5°	3.0
75°	2.2
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)